


The GB8LED Series is the ideal lighting solution for high quality, diffused lighting where minimal power requirements are desired. This LED GloBug series best supports applications such as security, emergency response, road and indoor, and equipment mount lighting.

- **Superior lighting properties** — Color consistency is near perfect, with better color rendering and overall quality
- **Impact resistant LED assembly** — Protects the lamps and is water resistant
- **Long life, low maintenance** — Up to 40,000 hours of operating life per bulb
- **Cooler lamp temperatures** obtained with LED (158 °F) allows for easier handling vs. metal halide (442 °F)
- **Optional illuminance settings** — 3-stage dimming controls (400W, 600W and 800W)
- **Convenient operation** — Instant start and restarting; no lighting delays
- **Environmentally, economically smart** — LED reduces operating costs and CO2 emissions up to 85%
- **Flexible set-up options** — Two position tripod stand, two stage (gas assist) vertical mast assembly
- **Self-inflating balloons** — Full inflation in less than 20 seconds
- **Easy transport and storage** — vinyl carrying cases included

Light Plot



Grid=20 ft.

Footcandle	10	5	2	1.0	0.5	0.25
Diameter (ft.)	34	40	60	68	76	132



GB8LED



GBC8LED

Shown with optional generator

Model	GB8LED	GBC8LED
Mount Type	Tripod, aluminum, 3-stage air-assisted mast	Cart, zinc plated steel w/ 3-stage air-assisted mast
Max. Height	13.2'	10.6'
Total Weight	48 lb.	127 lb.
Wind Limits	25 MPH	
Lamp Assembly		
Balloon	47" x 28"	
Lamp (W)	800W LED	
Lumens	110,000 (High)	
Voltage (V)	115	
Current (A)	6.9A @115V	
Hertz (Hz)	50-60	
Dimmer Switch	400/600/800W	
Min. Generator	1200 W	

*Also available: **GB8LEDB** — 800W LED Balloon lamp assembly (Total weight: 25 lb.)*