





H₂S, CO, O₂, LEL





Go the distance, and save

GasAlertMax XT II is the smart, simple, economical way to compliance. Workers feel safe and incidents are minimized so everyone will be able to do more. That means savings realized from business continuity and productivity.

Simple operation, with SmartSample pump.

GasAlertMax XT II reliably monitors up to four hazards and combines straightforward one-button operation, a robust, motorized pump for remote sampling, and now features IntelliFlash, the flashing LED compliance indicator that tells you at-a-glance your gas detector is functioning correctly. The GasAlertMax XT II is fully compatible with MicroDock II automated test and calibration system.

Standard Package Contents

- Detector complete with specified sensor(s), stainless steel alligator clip and concussion-proof housing
- Rechargeable battery
- Wall outlet charging adaptor
- 3 ft. / 1 m calibration hose with quick connect
- 10 ft. / 3 m sampling hose with particulate filter and quick connect
- Reversible screwdriver
- Kit of spare pump filters (5 particulate and 5 hydrophobic)
- Manual
- Multi-language CD manual

General Specifications

•		
Size	5.1 x 2.8	x 2.0 in. / 13.1 x 7.0 x 5.2 cm
Weight	11.5 oz. /	′ 328 g
Typical battery life	13 hours @ 32°F / 0°C 8 hours @ -4°F / -20°C Recharges in 6 hours	
Certifications and approvals	.	Class I, Div. 1, Gr. A, B, C, D
арр. отао	IECEx:	Ga Ex ia IIC T4
	ATEX:	C €
	INMETR	O: BR-Ex ia IIC T4
Warranty	Full two y	ear warranty including all sensors

6570-0



36 5062-26-NCL-EN



Order Number

GasAlertMax XT II 4-Gas Detector	Yellow	Black
%LEL, O ₂ , H ₂ S, CO	XT-XWHM-Y-NA	XT-XWHM-B-NA
GasAlertMax XT II 3-Gas Detector	Yellow	Black
%LEL, O ₂ . H ₂ S	XT-XWH0-Y-NA	XT-XWH0-B-NA
%LEL, O ₂ , CO	XT-XW0M-Y-NA	XT-XW0M-B-NA
O ₂ , H ₂ S, CO	XT-X0HM-Y-NA	XT-X0HM-B-NA
GasAlertMax XT II 2-Gas Detector	Yellow	Black
%LEL, O ₂	XT-XW00-Y-NA	XT-XW00-B-NA
H₂S, CO	XT-00HM-Y-NA	XT-00HM-B-NA
O ₂ , H ₂ S	XT-X0H0-Y-NA	XT-X0H0-B-NA
O ₂ , CO	XT-X00M-Y-NA	XT-X00M-B-NA
GasAlertMax XT II 1-Gas Detector	Yellow	Black
O ₂	XT-X000-Y-NA	XT-X000-B-NA
H ₂ S	XT-00H0-Y-NA	XT-00H0-B-NA
CO	XT-000M-Y-NA	XT-000M-B-NA

GasAlertMax XT II Region Codes

For orders outside North America, change order number suffix "-NA" to:						
"-EU"	Europe	"-BR"	Brazil			
"-UK"	United Kingdom	"-OR"	Other region with 3-pin UK plug			
"-AU"	Australia	"-OE"	Other region with 2-pin UK plug			
"-CN"	China/New Zealand					

Gas Legend

	_
%LEL	Combustible (W)
O ₂	Oxygen (X)
H ₂ S	Hydrogen sulfide (H)
CO	Carbon monoxide (M)





MicroDock II

Automatic test and calibration station
(see MicroDock II section for additional information)

5062-26-NCL-EN 37

IQ Force™		Lead Time (days)	Max Qty
IQ-XWY-B-NA	%LEL, O ₂ , H ₂ S, CO, rechargeable battery	2	10*
All other configurations	IQ Force™	8	100**
MultiPro™		Lead Time (days)	Max Qty
54-48-314NDY	%LEL, O_2 , Duo-Tox (CO/ H_2S), rechargeable battery, datalogging and vibrating alarm	2	10*
54-48-314ADY	%LEL, O_2 , Duo-Tox (CO/ H_2S), alkaline battery, datalogging and vibrating alarm	2	10*
All other configurations	MultiPro™	13	25**
GasAlertMax XT II		Lead Time (days)	Max Qty
XT-XWHM-Y-NA	%LEL, O ₂ , H ₂ S, CO detector	2	20*
XT-XWHM-Y-NA-CS	%LEL, O ₂ , H ₂ S, CO detector, with confined space kit	2	4*
All other configurations	GasAlertMax XT II	8	100**
Impact & Impact Pro		Lead Time (days)	Max Qty
2302B20008UE	Impact	2	20*
2302B20009UE	Impact Pro	2	50*
GasAlertMicro 5 Series		Lead Time (days)	Max Qty
M5-XW0Y-R-P-D-Y-N-00	%LEL, O ₂ , H ₂ S, CO detector, rechargeable battery, pump and datalogging	2	3*
M5-XWSY- R-P-D-Y-N-00	%LEL, O ₂ , H ₂ S, CO, SO ₂ detector, rechargeable battery, pump and datalogging	2	2*
M5PID-XWQY-R-P-D-Y-N-00	VOCs, %LEL, O ₂ , H ₂ S, CO detector, rechargeable battery, pump and datalogging	2	3*
All other configurations	GasAlertMicro 5 Series	8	25**
PhD6™		Lead Time (days)	Max Qty
Standard configurations	PhD6™	8	15*
MicroMAX Pro		Lead Time (days)	Max Qty
MPRO-4ABCD	MicroMAX Pro O ₂ LEL CO H ₂ S	2	20*
All other configurations	MicroMAX Pro	20	50*

5062-26-NCL-EN 103