

## SPECIFICATIONS

## Certifications/Qualifications

[www.kichler.com/warranty](http://www.kichler.com/warranty)

## Dimensions

Base Backplate	5.00 DIA
Extension	8.00"
Weight	5.10 LBS
Height from center of Wall opening (Spec Sheet)	4.00"
Height	9.25"
Width	24.00"

## Light Source

Lamp Included	Not Included
Lamp Type	A19
Light Source	Incandescent
Max or Nominal Watt	75W
# of Bulbs/LED Modules	3
Socket Type	Medium
Socket Wire	150"

## Mounting/Installation

Install Glass Up or Down	Yes
Interior/Exterior	Interior
Location Rating	Damp
Mounting Weight	2.40 LBS

## FIXTURE ATTRIBUTES




## Housing

Diffuser Description	Clear Seeded
Primary Material	STEEL

## Product/Ordering Information

SKU	45973NI
Finish	Brushed Nickel
Style	Industrial
UPC	783927551915

## Finish Options

-  Brushed Nickel
-  Natural Brass
-  Olde Bronze



## ALSO IN THIS FAMILY



43850NBR



43851NBR



42296NBR



45971NBR



43853NBR



45972NBR