

## SPECIFICATIONS

## Certifications/Qualifications

[www.kichler.com/warranty](http://www.kichler.com/warranty)

## Dimensions

Base Backplate	5.00 DIA
Weight	2.00 LBS
Height	8.50"
Overall Height	125.00"
Width	8.00"

## Light Source

Lamp Included	Not Included
Lamp Type	A19
Light Source	Incandescent
Max or Nominal Watt	100W
# of Bulbs/LED Modules	1
Socket Type	Medium
Socket Wire	105"

## Mounting/Installation

Interior/Exterior	Interior
Location Rating	Dry
Mounting Style	Cord
Mounting Weight	1.10 LBS

## FIXTURE ATTRIBUTES

## Housing

Diffuser Description	Clear Seeded
Primary Material	GLASS

## Product/Ordering Information

SKU	43850CH
Finish	Chrome
Style	Industrial
UPC	783927469067

## Finish Options

-  Brushed Nickel
-  Chrome
-  Natural Brass
-  Olde Bronze



## ALSO IN THIS FAMILY



43850NBR



43851NBR



42296NBR



45971NBR



43853NBR



45972NBR