

**SPECIFICATIONS**

<b>Certifications/Qualifications</b>	
	<a href="http://www.kichler.com/warranty">www.kichler.com/warranty</a>
<b>Dimensions</b>	
Base Backplate	5.50 DIA
Extension	6.50"
Weight	4.00 LBS
Height from center of Wall opening (Spec Sheet)	4.50"
Height	10.25"
Width	23.75"
<b>Light Source</b>	
Lamp Included	Not Included
Lamp Type	A19
Light Source	Incandescent
Max or Nominal Watt	100W
# of Bulbs/LED Modules	3
Socket Type	Medium
Socket Wire	150"
<b>Mounting/Installation</b>	
Install Glass Up or Down	Yes
Interior/Exterior	Interior
Location Rating	Damp
Mounting Style	Wall Mount
Mounting Weight	2.40 LBS

**FIXTURE ATTRIBUTES**

<b>Housing</b>	
Diffuser Description	Clear Seeded
Primary Material	STEEL
<b>Product/Ordering Information</b>	
SKU	45392CH
Finish	Chrome
Style	Transitional
UPC	783927517942

**Finish Options**

-  Black
-  Brushed Nickel
-  Chrome
-  Classic Bronze



**ALSO IN THIS FAMILY**

