

# Avery 14.75" 2 Light Vanity Light with Clear Seeded Glass Brushed Nickel

45972NI

© 2021 Kichler Lighting LLC. All Rights Reserved.

## SPECIFICATIONS

### Certifications/Qualifications

[www.kichler.com/warranty](http://www.kichler.com/warranty)

### Dimensions

Base Backplate	5.00 DIA
Extension	8.00"
Weight	3.10 LBS
Height from center of Wall opening (Spec Sheet)	4.00"
Height	9.25"
Width	14.75"

### Light Source

Lamp Included	Not Included
Lamp Type	A19
Light Source	Incandescent
Max or Nominal Watt	75W
# of Bulbs/LED Modules	2
Socket Type	Medium
Socket Wire	150"

### Mounting/Installation

Install Glass Up or Down	Yes
Interior/Exterior	Interior
Location Rating	Damp
Mounting Weight	1.30 LBS

## FIXTURE ATTRIBUTES




### Housing

Diffuser Description	Clear Seeded
Primary Material	STEEL

### Product/Ordering Information

SKU	45972NI
Finish	Brushed Nickel
Style	Industrial
UPC	783927551892

### Finish Options

-  Brushed Nickel
-  Natural Brass
-  Olde Bronze



## ALSO IN THIS FAMILY



43850NBR



43851NBR



42296NBR



45971NBR



43853NBR



45972NBR