

MOTOR FINISH



Satin Natural Bronze

BLADE FINISHES

Walnut, Cherry



AIR PERFORMANCE

AIRFLOW Cubic Ft. Per Minute on High	RPM Revolutions Per Minute on High	POWER USAGE Watts on High (Excludes Lights)	AIRFLOW EFFICIENCY Cubic Ft. Per Minute Per Watt	CFM (Low)	1523
4200	161	52	81	RPM (Low)	57
				Watts (Low)	9

SPECIFICATIONS

Light Source			
Downward-facing Bulbs	3 X 4	Downlight Included	Yes
Downlight Option	Removable	Watts (High)	52
Watts (Low)	9		
Photometrics			
Color Rendering Index	80	Kelvin Temperature	2700K
Electrical			
Amps (High)	0.43	Amps (Low)	0.07
Motor Size	153MM X 15MM	Motor Type	AC
Dimensions			
Base Backplate	5.25 DIA	Downrod 1	1.00 OD X 4.00"
Downrod 1 - Measurement A	14.50"	Downrod 1 - Measurement B	7.50"
Downrod 1 - Measurement C	11.50"	Weight	19.71 LBS
Height	17.50"	Width	52.00"
Mounting/Installation			
Minimum Distance from Fan to Floor	7 feet	Interior/Exterior	Interior
Lead Wire Length	78"	Location Rating	CSA UL Listed Dry
Low Ceiling Adaptable	Yes, Dual Mount Included	Mounting Weight	15.09 LBS

FIXTURE ATTRIBUTES

Product/Ordering Information			
SKU	330017SNB	Finish	Satin Natural Bronze
Style	Traditional	UPC	783927586542
Housing			
Diffuser Description	White Etched	Primary Material	STEEL
Max Stem Tilt	22 Degrees		

Blade Finish & Specs

Blade Finish 1	WALNUT	Blade Finish 2	CHERRY
Blade Material	WOOD	Blade Pitch	12
Blades Included	Yes	Blade Sweep	52
Number of Blades	5	Blades Reversible	Yes

Warranty

www.kichler.com/warranty

ALSO IN THIS FAMILY



330017MWH



330017NI



330017SBK



330017WH

You can see all products in this family by searching **Kichler.com**