



SPECIFICATIONS

Product Description: **DUCTING, STATICALLY CONDUCTIVE, 8" (20.3 cm) DIAMETER**
Part Number: **9500-15EX, 9500-25EX**
Style: **RETRACTABLE**

GENERAL DESCRIPTION:

This product is lightweight, retractable and designed for maximum air handling capabilities. Dual direction flow with low friction loss while providing a safe positive means of discharging static build-up.



CONSTRUCTION:

- Vinyl and polyester anti-static materials
- Single-Ply
- Neoprene coated
- -65° F to 250° F (-53° C to 121° C) temperature range
- Retractable, Non-collapsible design.
- Class 1 hard drawn spring steel wire helix
- Meets ASTM 227 Specs
- Meets flame retardant requirements of UL94 V-0
- Rated to 100,000 OHMS or less per square inch
- Integrated with extended solid grounding wire at each end

AVAILABLE:

Part No.	Diameter	Length	End-Straps
9500-15EX	8" (20.3 cm)	15' (4.57 m)	Dual
9500-25EX	8" (20.3 cm)	25' (7.62 m)	Dual

ACCESSORIES:

Part No.	Ducting Size	Description
9500-01	8" (20.3 cm)	Duct to Duct Connector, with raised lip
9500-35	8" (20.3 cm)	Storage Rack for 8" (20.3 cm) Ducting, up to 25' (7.62 m) Ducting
9500-45	8" (20.3 cm)	Storage Bag
9600-50EX	8" (20.3 cm)	Reducer, Statically conductive for 16" (40.6 cm) blower