



# **SPECIFICATIONS**

Product Description: VENTILATION BLOWER, HIGH OUTPUT, EXPLOSION-PROOF

Part Number: 9515-50EX

Style: AXIAL FAN 16" (40.6 cm)

#### **GENERAL DESCRIPTION:**

Designed for applications requiring a maximum amount of output. Made from 16-gauge cold rolled steel housing and powder-coated in safety orange with 3 blade impeller. Powered by a 1 ½ hp, 3450 RPM UL listed, IECEx/ATEX/INMETRO certified motor. Comes with an interchangeable flange for intake or exhaust mounting, integrated carry handles for easy transport and a steel/zinc plated grill. Four rubber feet, built in on/off switch and voltage change switch are added features of this powerhouse unit.

#### **CONSTRUCTION:**

- Complete unit epoxy powder-coated in orange
- Interchangeable flange for intake or exhaust side mounting
- 16-gauge cold rolled steel housing
- Integrated carry handles
- Steel grill (zinc plated), equipped with four rubber feet
- Built-in "on/off" switch
- Duct grounding lug
- NOTE: EX blowers require an explosion-proof socket (9503-03)

## **MOTOR:**

HP: 1 ½ HP

Certifications: UL Listed, IECEx/ATEX/INMETRO Certified

Voltage/Hz: 115/230V AC, 50/60 Hz, Single Phase (Integrated voltage selector)

RPM: 3450

Current Draw: 15.5/7.8A (60 Hz)

Cord: 25' (7.63 m) 12/3 AWG MTW 90C 600V

Plug: NEMA 20 Amp, 125V or 250V plug, Explosion Proof rated

Protection: Thermal, Automatic Reset

# FAN:

• Anti-Static glass reinforced polyamide (PAGAS) three blade fan with aluminum hub

#### **ACCESSORIES:**

## Ducting

- Black, single-ply, neoprene coated, statically conductive vinyl/polyester material, temp. resistant up to 250°F (121.1°C)
- Retractable, non-collapsible design, Class 1 hard drawn spring steel wire helix (meets ASTM 227 specs)
- Grounding cable on both ends
- WARNING: When using statically conductive ducting, the integrated grounding wire must be properly
  grounded to the blower chassis <u>OR</u> linked to any additional grounding wire or duct used (as shown).
   Refer to User Manual for detailed instructions.



#### EX Rated Receptacle

- Iron mounting box with triple coat finish and spring-loaded door to keep out dust when in use. When plug is not in use, a neoprene gasket inside receptacle seals around plug to keep out dirt, water, dust, etc.
  - o 9503-03: 125V only
  - o 9503-06: 250V only

#### EX Rated Extension Cords

9540-50EX: 115V9540-60EX: 230V

# **HAZARDOUS LOCATION RATING:**

Motors			EX Plugs		
	ATEX	II 2 G Ex d Gb	NEC 500 Class I, Group B, C, D Class II, Group F&G		
	IECEx	Ex d IIB Gb	NEC 505 Class I, Zone 1, Group IIB & H2		
	INMETRO	Ex d IIB Gb			

Continued on Page 2

1360 Shiloh Church Road Piedmont, SC 29673 864-846-8740 800-622-3530 FAX: 800-362-7231 <u>www.allegrosafety.com</u>

# **BLOWER DIMENSIONS:**

Length	Width	Height	Weight
18" (45.7 cm)	18" (45.7 cm)	19" (48.2 cm)	62 lbs. (28.12 kg)

# FLOW RATES: (CFM calculated using 15' (4.57 m) of 16" (40.6 cm) ducting)

Free Air CFM	One 90° Bend	Two 90°Bends
4839 CFM (8226.30 m <sup>3</sup> /hr)	2942 CFM (5001.40 m <sup>3</sup> /hr)	2926 CFM (4974.20 m <sup>3</sup> /hr)

1360 Shiloh Church Road Piedmont, SC 29673 864-846-8740 800-622-3530 FAX: 800-362-7231 <u>www.allegrosafety.com</u>

Rev L 10-28-19