

NOW AVAILABLE

RAVEN™ 100 Count Boxes



POWDER-FREE NITRILE DISPOSABLE GLOVES



Powder Free

Examination Grade

Latex Free

Textured Grip

Single Use Only



Raven™ Extra Strength Disposable Gloves

- Powder-free exam grade nitrile
- Thickness: 6 mil
- Non-latex
- Outstanding strength, wear and dexterity
- Fully textured for enhanced gripping power
- 100 gloves per box

Powder-Free

Item No.	Size
S66516	Small
S66517	Medium
S66518	Large
S66519	X-Large
S66520	2X-Large

Particular		Raven minimum specifications	ASTM
Palm width (mm)	Small	85 ± 5	80 ± 10
	Medium	95 ± 5	95 ± 10
	Large	105 ± 5	111 ± 10
	X-Large	115 ± 5	120 ± 10
	2X-Large	120 ± 5	N/A
Length (mm)		245 - 5 / + 7	min. 220-230
Thickness (Single Wall)		6 mil	2 mil
Tensile Strength	Before aging (MPa)	min. 14	min. 12.5
	After aging (MPa)	min. 14	min. 12.5
Elongation	Before aging (%)	500	500
	After aging (%)	400	400