



Diablo BiMetal Recip Solution: Wood Demolition/Nail Embedded





for less heat, gumming

& corrosion

Fast Plunging
Tip



Demolition Blade Body

for straighter cuts with

less vibration

Progressive Tooth Design

aggressively spaced teeth (increasing TPI from tip to shank) for 5x longer cutting life

•Lengths: 6, 9, 12

•Pack Sizes: 1, 2, 5, 25, 200

•TPI: 4/6

Ultra Hardened Cutting Edge

for extreme durability and maximum performance (62 HRC versus 55 HRC)

9" and 12" with a slightly thicker 1.6mm Blade Body



Diablo BiMetal Recip Solution:





Demolition

Blade Body

for straighter cuts with less

vibration

Ultra Hardened Cutting Edge

for extreme durability and maximum performance (62 HRC versus 55 HRC)

Perma-Shield Coating

for less heat, gumming & corrosion

For clean and nail embedded wood, metals, plastics

Lengths: 6, 9, 12

Tooth Design: Dual Tooth

TPI 8/14

Pack Sizes: 1, 2, 5, 25, 200

Fast Plunging Tip

Progressive Tooth

Design aggressively spaced teeth (increasing TPI from tip to shank) for 5x longer cutting life






Diablo BiMetal Recip Solution:










Faster Cuts in Fewer Passes Resulting in Less Heat Build-up for 5x Longer Cutting Life

V.S.



Slower Cutting & More Heat Build-up for Decreased Blade Life Unique tooth configuration for smoother cuts with less vibration

Medium Metal

- Length 4, 6. 9 12"
- Dual Tooth Design for smooth cuts with less vibration.
- Full Contact Arch Design
- TPI 14/18
- Material Thicknesses: 1/16" to 5/16"
- Pack Sizes: 1, 2, 5, 25, 200

