

DELTA LEVER

A clean, streamlined design, Delta fits a whole range of decorating styles beautifully, from traditional to contemporary.

- Featuring SmartKey Security[™]
- ANSI/BHMA Grade 3 Certified Security
- ADA Compliant





Delta™ Lever in Polished Chrome

Specifications

Door Prep	Cross Bore 2-1/8". Edge bore 1".		
Backset	Adjustable $2^{-3}/8$ " or $2^{-3}/4$ ". UL functions $2^{-3}/4$ " standard or $2^{-3}/8$ " optional.		
Door Thickness	1- ³ / ₈ " - 1- ³ / ₄ " Doors standard.		
Cylinder	SmartKey Security [™] or Traditional 5-pin Pin & Tumbler		
Faceplates	1" x 2-1/4" Specify round corner or square corner. Also available as drive-in latch.		
Strikes	2-1/4" Full lip standard. Specify round corner, square corner. Other options available.		
Bolt	1/2" Throw		
ANSI/BHMA	A156.2 Grade 3 (all functions except 488)		
ADA	200 function satisfies section 4.13.9 ADA requirements.		
UL	Meets 3-hour fire rating for all UL specific functions.		

Functions



Passage/Hall/Closet: Both levers always free



Privacy/Bed/Bath: Both levers locked or unlocked by turnbutton inside. Outside lever unlocked by emergency key



Keyed Entry Lever: Both sides locked or unlocked by key outside or turnbutton inside



Free Interior:

Outside locked or unlocked by key outside or turn button inside. Inside always free.



Storeroom/Vestibule:


Outside unlocked only while key is turned. Inside always free



Half Dummy Trim, Surface Mounted:

For doors where only a pull is required. No operation

Dimensions



Design	Α	В	С	C (Keyed)
Delta™	2 5/8"	3 5/8"	1 ⁷ /s"	2 5/8"









Delta™ Lever in Venetian Bronze

LIFETIME WARRANTY

Finishes



Polished Brass 3



Antique Brass **5**



Venetian Bronze 11P



Satin Nickel 15



Antique Nickel 15A



Polished Chrome 26



Satin Chrome 26D