


7775693
FF525C



52" Five-Blade Ceiling Fan, Brushed Chrome



PRODUCT SPECIFICATIONS

FEATURES	DESCRIPTION
Mounting Type	Dual-Mount
Fan Span	52"
No. of Blades	5
Product Use	Residential
Light Kit	Frosted
Body Color	Brushed Chrome Finish
Blade Color(s)	Gray Wood Grain
Blade Pitch	10.5°
Rotation	Reversible
Lamp Source	LED lighting Plate*22w*3,000k *10.000 Hrs
Downrod	6"L X 1/2"D
Blade Material	Plywood
Speed	3
Pull Chain or Remote Control	Pull Chain Switch
Clearnace (B)	11.5"
Motor Size (MM)	153*15
Motor Diameter (C)	10.2"
Bulbs Included	Yes
AMPS (HI speed)	<1
Watts (Hi speed)	56.8
Airflow (Cu. Ft. Per Minute)	2891
Airflow Efficiency (CFM Per Watt)	78

SUBMITTAL SHEET

- Dual-mount
- 3-speed reversible motor
- Brushed Chrome finish
- Frosted glass light kit
- 22W LED lighting palte
- 3,000 kelvin
- 10,000 average hour life
- Five blades


SAMPLE SPECIFICATION:

Ceiling fan shall be
7775693,52"five-blade in
Brushed Chrome finish.

7775693
FF525C



Abano de Cinco Hojas de Montaje Hugger,52"Acabado Cromo Cepillado



ESPECIFICACIONES DEL PRODUCTO

FEATURES	DESCRIPCIÓN
Tipo del Montaje	Montaje Doble
Fan span (D)	52"
Numero de Hojas	5
Uso del Producto	Residencial
Kit de Lux	Esmerilado
Color del Cuerpo	Cromo Cepillado
Color de la Hoja	Grano de madera gris
Paso de la Hoja	10.5°
Rotación	Reversible
Fuente de Lámpara	Placa de Iluminación LED*22W*3,000K *10,000Hrsrs
Varilla	6"L x 1/2"D
Material de Hoja	Madera Contrachapada
Velocidad	3
Cadena Tirada o Control Remoto	Interrupdo de Cadena Tirada
Espacio (B)	11.5"
Tamaño del Motor (MM)	153*15
Diámetro del Motor (C)	10.2"
Bombillas Incluidas	Si
Amperios (Alta Velocidad)	<1
Vatios (Alta Velocidad)	56.8
Flujo (Pies Cúbicos por Minuto)	2891
Eficiencia del Flujo de Aire (Pies Cúbicos por MinutoCada Vatio)	78

TABLA DE PRESENTACIÓN

- Montaje doble
- Motor reversible de 3 velocidades
- Acabado Cromo Cepillado
- Luz de cristal esmerilado
- Placa de iluminación LED de 22W
- 3,000 kelvin
- Vida útil promedia de 10,000 horas.
- Cinco hojas

ESPECIFICACIONES DE MUESTRA:

El abano debe ser

7775693, de 52 pulgadas, cinco
hojas en Acabado Cromo Cepillado.