

MONSOON DCBL one-piece liner

Monsoon DCBL is one-of-a-kind. We started with a 715 CFM DC motor and added stainless steel baffle filters with a removable grease tray for easy cleaning. Then we introduced vertical and horizontal ducting to insert liner range hoods. We went beyond the expected by also equipping Monsoon DCBL with a wireless remote control, and finally, we challenged all conventional notions of performance by adding the proprietary DCBL Suppression System™ that makes Monsoon DCBL the most quiet and energy efficient insert liner available today. Never has an insert liner range hood been so technologically advanced.

	INTERNAL BLOWER STANDARD	ACT™ INTERNAL BLOWER with AIRFLOW CONTROL TECHNOLOGY™			
Min.-Max. CFM	250 - 715	Min.-Max. CFM	250 - 590	250 - 440	250 - 290
Min.-Max. Sones	0.8 - 5.8	Min.-Max. Sones	0.8 - 4.5	0.8 - 3	0.8 - 1.2

ACT is a feature built into all Zephyr hoods with DCBL Suppression System™ technology allowing you to limit the maximum blower CFM to meet local code requirements.



MATCHES CONVENTIONAL INSTALLATION DIMENSIONS



26" - 36" MOUNTING HEIGHT



Zephyr's wireless RF remote puts you in control of your one-piece liner from up to 15 feet away.

ADA
COMPLIANT

ZEPHYR

MONSOON DCBL | ONE-PIECE LINER


ESSENTIALS
EUROPA POWER BREEZE

SIZE	
AK9428AS (30")	28-3/8" x 22-1/2"
AK9434AS (36")	34-3/8" x 22-1/2"
AK9440AS (42")	40-3/8" x 22-1/2"
PERFORMANCE	
INTERNAL, MIN.-MAX. BLOWER CFM	250 - 715
INTERNAL, MIN.-MAX. SONES	0.8 - 5.8
COLOR	
STAINLESS STEEL	SS
FEATURES	
CONTROLS	Electronic LCD
SPEED LEVELS	5 + Burst
AUTO DELAY-OFF	Yes
CLEAN AIR MODE	Yes
LIGHTING	Bloom™ HD LED 6W x 2
AK9428AS / AK9434AS	Bloom™ HD LED 6W x 3
AK9440AS	
DUAL LEVEL LIGHTING	Yes
FILTERS	SS Pro-Baffle
REMOVABLE GREASE TRAY	Yes
RF REMOTE CONTROL	Yes
RECIRCULATING OPTION	No
DUCT SPECIFICATIONS	
VERTICAL - INTERNAL	8" Round
HORIZONTAL - INTERNAL	3-1/4" x 10" Rectangular, 8" Round
AC INPUT	
	120V - 60Hz
AC POWER	
AK9428AS / AK9434AS	Max. 219W at 3.5A
AK9440AS	Max. 225W at 3.6A
MOUNTING HEIGHT*	
	26" - 36"
WARRANTY	
	3 Years Parts, 1 Year Labor


*Mounting height refers to distance between top of a 36" tall cooking surface and bottom of custom hood.

Specifications subject to change, check zephyronline.com for up to date information.


VERTICAL AND
HORIZONTAL
DUCTING



FRONT



TOP



BACK



All Next Generation Europa range hoods are equipped with DCBL Suppression™ technology, including Bloom™ HD LED light bulbs. To learn more, visit us at zephyronline.com.



ZEPHYR