
## 9205175 FLCL1014LEDBN

LED FLAT PANEL







## PRODUCT SPECIFICATIONS

	11
FEATURES	1' x 4' LED FLAT PANEL LIGHT
Part Number	FLCL1014LEDBN
Finish	Brushed Nickel
Kelvin Temp (CCT)	4000K
Product Dimensions	48"L x 12.1"W x 2"H
Product Weight	10.45 lbs
Bulb Type	Integrated LED Module
Bulb Included	Yes
LED Type	SMD2835
CRI	90
Lumens	4100
Efficacy	100 lm/W
Dimmable	0-10V
Wattage	40
Equivalent Wattage	Incandescent-200W
Voltage	AC120-277V
Average hour life	50,000 hrs
Min/Max Ambient Temp	-20°C~50°C
Product Material	Aluminum, Plastic (PS)
Location Listing	Dry
Certifications	UL, Title24/JA8-2019, FCC

## FLCL1014LEDBN

LED Flat Panel Light

- Location:Dry
- Beam Angle: 120°
- Shell Material: Aluminum & High Quality LGP
- PF: ≥0.95
- 5 Year Warranty

## SPECIFICATION:

Light Fixture shall be 9205175/FLCL1014LEDBN , 1' x 4' LED Flat Panel