

For Cutting Concrete & Pipe

890 Series

The ICS 890 Series hydraulic cutting system offers the superior strength of FORCE4® technology and is equipped with integrated water delivery system that continuously feeds water to the blade. From the redesigned, more durable rear handle, to the easy to replace drive sprocket, this hydraulic power cutter is engineered to stand up to your toughest jobs. In a package that exceeds industry standards, this sleek powerhouse is packed with features designed to make it work as hard as you do.



890F4 HYDRAULIC POWER CUTTERS AND CONSUMABLES*

| PART NUMBER | DESCRIPTION | PART NUMBER | DESCRIPTION |
|-------------|---|-------------|--|
| 566110 | ICS 890F4 Powerhead 8 gpm/30 lpm, 1 ft/30 cm hose whips | 531743 | ICS FORCE4-25 chain 10 in/25 cm |
| 566355 | ICS 890F4 Powerhead 8 gpm/30 lpm, 8 ft/2.5m hose whips | 525342 | ICS FORCE4-29 chain 15 in/38 cm |
| 566112 | ICS 890F4 Powerhead 12 gpm/45 lpm, 1 ft/30 cm hose whips | 531749 | ICS FORCE4-34 chain 20 in/50 cm |
| 566116 | ICS 890F4 Powerhead 12 gpm/45 lpm, 8 ft/2.5m hose whips | 525345 | ICS FORCE4-40 chain 25 in/63 cm |
| 566113 | ICS 890F4-FLUSH Powerhead 8 gpm/30 lpm, 1 ft/30 cm hose whips | 531745 | ICS FORCE4-25 Premium L chain 10 in/25 cm |
| 566351 | ICS 890F4-FLUSH Powerhead 8 gpm/30 lpm, 8 ft/2.5m hose whips | 525343 | ICS FORCE4-29 Premium L chain 15 in/38 cm |
| 566114 | ICS 890F4-FLUSH Powerhead 12 gpm/45 lpm, 1 ft/30 cm hose whips | 531751 | ICS FORCE4-34 Premium L chain 20 in/50 cm |
| 566117 | ICS 890F4-FLUSH Powerhead 12 gpm/45 lpm, 8 ft/2.5m hose whips | 525346 | ICS FORCE4-40 Premium L chain 25 in/63 cm |
| 566127 | ICS 890F4-15 Package 8 gpm/30 lpm, 1 ft/30 cm hose whips, case | 531739 | ICS FORCE4-25 Premium S chain 10 in/25 cm |
| 566717 | ICS 890F4-15 Package 8 gpm/30 lpm, 8 ft/2.5m hose whips, case | 531735 | ICS FORCE4-29 Premium S chain 15 in/38 cm |
| 566123 | ICS 890PG-15 Package 8 gpm/30 lpm, 1 ft/30 cm hose whips, case | 531741 | ICS FORCE4-34 Premium S chain 20 in/50 cm |
| 566710 | ICS 890PG-15 Package 8 gpm/30 lpm, 8 ft/2.5m hose whips, case | 531737 | ICS FORCE4-40 Premium S chain 25 in/63 cm |
| 566125 | ICS 890PG-15 Package 12 gpm/45 lpm, 1 ft/30 cm hose whips, case | 531747 | ICS FORCE4-25 Abrasive chain 10 in/25 cm |
| 566712 | ICS 890PG-15 Package 12 gpm/45 lpm, 8 ft/2.5m hose whips, case | 525344 | ICS FORCE4-29 Abrasive chain 15 in/38 cm |
| 566124 | ICS 890PG-20 Package 8 gpm/30 lpm, 1 ft/30 cm hose whips, case | 531753 | ICS FORCE4-34 Abrasive chain 20 in/50 cm |
| 566711 | ICS 890PG-20 Package 8 gpm/30 lpm, 8 ft/2.5m hose whips, case | 525347 | ICS FORCE4-40 Abrasive chain 25 in/63 cm |
| 566126 | ICS 890PG-20 Package 12 gpm/45 lpm, 1 ft/30 cm hose whips, case | 537764 | ICS PowerGrit Chain 15 in/38 cm |
| 566716 | ICS 890PG-20 Package 12 gpm/45 lpm, 8 ft/2.5m hose whips, case | 537765 | ICS PowerGrit Chain 20 in/50 cm |
| 529829 | ICS 890F4 Guidebar 10 in/25 cm | 545017 | ICS PowerGrit Chain 25 in/63 cm |
| 523080 | ICS 890F4 Guidebar 15 in/38 cm | 571504 | ICS FORCE4-25 Premium S wide kerf (.375) chain 10 in/25 cm |
| 529767 | ICS 890F4 Guidebar 20 in/50 cm | 570943 | ICS FORCE4-29 Premium S wide kerf (.375) chain 15 in/38 cm |
| 525320 | ICS 890F4 Guidebar 25 in/63 cm | 571505 | ICS FORCE4-34 Premium S wide kerf (.375) chain 20 in/50 cm |
| | | 571506 | ICS FORCE4-40 Premium S wide kerf (.375) chain 25 in/63 cm |
| | | 565065 | ICS 890F4 Drive Sprocket |
| | | 565066 | ICS 890F4-FLUSH Drive Sprocket |
| | | 70636 | 890F4 Tensioner Kit |
| | | 523946 | 890F4-FL Tensioner Kit |
| | | 70619 | Tensioning Srench |

See the entire list of our guidebar and chain compatibility on pages 22-23.