

SPECIFICATIONS

Certifications/Qualifications

www.kichler.com/warranty

Dimensions

Base Backplate	5.00 DIA
Extension	6.25"
Weight	4.60 LBS
Height from center of Wall opening (Spec Sheet)	4.00"
Height	8.25"
Length	30.00"
Width	5.00"

Light Source

Bulb Product ID	5909.00
Lamp Included	Not Included
Lamp Type	MR16 COVER
Light Source	HAL
Max or Nominal Watt	50W
# of Bulbs/LED Modules	4
Socket Type	GU10
Socket Wire	200"

Mounting/Installation

Mountable on Wall or Ceiling	Yes
Interior/Exterior	Interior
Location Rating	Damp
Mounting Weight	3.10 LBS

FIXTURE ATTRIBUTES

Housing

Diffuser Description	Light Umber
Primary Material	STEEL
Max Stem Tilt	90 Degrees

Product/Ordering Information

SKU	7772OZ
Finish	Olde Bronze
Style	Contemporary
UPC	783927470094

Finish Options

- Brushed Nickel
- Olde Bronze



ALSO IN THIS FAMILY



5078NI



1672OZ



5078OZ



5079OZ



5079CH



3475NI