




MULTI FITTINGS

LAYING LENGTH

ISSUE DATE: OCT 30/17
SUPERCEDES: MAR 11/05

45° WYE (GxGxG)



INJECTION MOLDED FITTING (M)

	SIZE H1xH2xH3	PART NUMBER	A REF	C REF	D REF
M =	4x4x4	063304	10.250	6.125	7.375
M =	6x6x4	063307	12.375	6.500	9.000
M =	6x6x6	063306	14.875	9.000	10.750
<> M =	8x8x4	063294	13.375	6.500	10.625
M =	8x8x6	063296	15.750	8.875	12.250
M =	8x8x8	063298	19.000	12.125	13.875
M =	10x10x4	043311	17.250	9.375	12.500
M =	10x10x6	043312	17.125	9.375	13.875
M =	10x10x8	043313	22.875	15.000	15.000
M =	10x10x10	043308	22.875	15.000	17.000
M =	12x12x4	043319	18.125	9.375	14.500
M =	12x12x6	043276	18.250	9.375	15.875
M =	12x12x8	043314	26.750	17.875	16.375
M =	12x12x10	043315	26.750	17.875	18.000
M =	12x12x12	043309	26.750	17.875	20.000
M =	15x15x4	043320	22.250	12.750	15.000
M =	15x15x6	043153	22.250	12.750	16.750
M =	15x15x8	043316	22.250	12.750	19.000
M =	15x15x10	143317	31.625	22.250	20.000
M =	15x15x12	143318	31.625	22.250	24.375
M =	15x15x15	143310	31.625	22.250	23.875

Note: = Refer to Page G4 for Hub Detail, Type A
<> 4" Deep hub