0114 Supersedes New

FM2800

Product information presented here reflects conditions at time of publication. Consult factory regarding discrepancies or inconsistencies.




TECHNICAL DATA SHEET



Models 202, 203, 204 Qwik Jon® Ultima Designed to accomodate a toilet, lavatory, bath tub and/or shower.

PRODUCT SPECIFICATIONS

MOTOR	Horse Power	1/2	
	Voltage	115	
	Phase	1 Ph	
	Hertz	60 Hz	
	RPM	3450	
	Туре	Permanent split capacitor	
	Insulation	Class B	
	Amps	7.0 - 10.5	
PUMP	Operation	Automatic	
	Discharge Size	1"	
	Solids Handling	Grinder	
	Cord Length	9' (3 m) standard	
	CordType	UL listed neoprene cord and plug	
	Certification	cCSAus (pump only)	
	Max. Head	30' (9.1 m)	
	Max. Flow Rate	45 GPM (17 LPM)	
	Max. Operating Temp.	130°F (54°C)	
	Cooling	Oil filled	
	Motor Protection	Auto reset thermal overload	
	Сар	Engineered plastic	
	Motor Housing	Cast iron	
	Pump Housing	Engineered plastic	
40	Tank	ABS	
MATERIALS	Upper Bearing	Ball bearing	
	Lower Bearing	Ball bearing	
	Mechanical Seals	Carbon/ceramic	
	Impeller Type	Non-clogging vortex	
	Impeller	Engineered plastic	
	Hardware	Stainless steel	
	Motor Shaft	AISI 1215	
	Gasket	Closed cell tank gasket; Buna-N pump o-rings	










Patent No. 7,203,976 Other Patents Pending

TOTAL DYNAMIC HEAD FLOW PER MINUTE

МО	DEL	202/203/204		
Feet	Meters	Gal.	Liters	
5	1.5	45	170	
10	3.0	40	151	
15	4.6	35	132	
20	6.1	27	102	
25	7.6	16	61	
Shut-off F	lead:	30 ft. (9.1 m)		



018512

Qwik Jon® Ultima systems include:

Model 202: tank, mini grinder pump and a comfort height, ADA compliant, rear outlet toilet with elongated bowl

Model 203: tank and mini grinder pump (standard rear outlet toilet with a discharge height of 4" (101.6 mm) from floor to centerline must be purchased separately)

Model 204: tank and mini-grinder pump without toilet inlet

SPECIFICATIONS

- Can be installed free-standing or behind a wall
- Discharge can be reduced to 3/4" to replace existing systems
- Pumps any direction
- Shipping Weight:

Model 202: 121 lbs. (55 kg) Model 203: 37 lbs. (17 kg) Model 204: 33 lbs. (15 kg)

 TANK: (2) 1-1/2" (DN40) slip / 2" MPT auxilary inlets and 1-1/2" (DN40) vent. Available in 1.6 GPF (6.1 LPF) or 1.28 GPF (4.8 LPF) systems

OPTIONS

- Standard Grinder Blade: Metal-stamped cutter plate handles typical toilet sewage. Dual cutting channels provide over 70,000 cuts / minute. (Figure 1)
- Premium Grinder Blade: Investment-cast 440 stainless steel cutter plate is engineered to handle cloth, latex and other hard to grind materials. Tri-Slice® CutterTechnology - three independent cutting channels provide over 250,000 cuts / minute. (Figure 2)
- Qwik Jon® Ultima extension kit for model 202, for behind-the-wall installations. P/N 10-2123*

^{*} Not IAPMO approved.







FIGURE 2



Model 202 meets the Americans with Disabilities Act guidelines and ANSI A117.1 requirements for accessible and usable facilities—check local codes. ▲ CAUTION All installation of controls, protection devices and wiring should be done by a qualified licensed electrician. All electrical and safety codes should be followed including the most recent National Electrical Code (NEC) and the Occupational Safety and Health Act (OSHA).