

14/3 Heavy Duty Outdoor Extension Cord



RAP31401, RAP31402



Model Numbers

- RAP31402 50FT 14/3 SJTW BLUE/YELLOW EXTRA-HEAVY DUTY OUTDOOR EXTENSION CORD
- RAP31401 100FT 14/3 SJTW BLUE/YELLOW EXTRA-HEAVY DUTY OUTDOOR EXTENSION CORD

Product Features

- **Power Indicator Light** – Allows user to see when the power is “on”
- **Water Resistant** – Jacket will not absorb water that can corrode copper conductors or cause dangerous electrical shocks
- **Flame Retardant** – Jacket compound is designed to not allow burning to spread. The compound is formulated to cause the flame to burn out before spreading further on the cord.
- **Superior Flexibility at Sub-Freezing Temperatures** – This cord is designed to maintain flexibility and resist cracking in temperatures down to -40°F (-40°C) and resists heat up to 140°F (60°C).
- **Meets OSHA Requirements** for extension cords and adapters for use on job sites.
- **UL/cUL Tested** to both U.S. and Canadian standards
- **NEMA Plug Configuration** – 5-15P to 5-15R
- **Electrical Ratings** – 15A/125V/1875W

Warranty

Subject to the limitations expressed herein, Seller warrants to the original Buyer that hand tools manufactured and sold by Seller (“Tool”) shall be free from defects in design, material and workmanship under Normal Use for the life of tool. This warranty is void for any damage caused by misuse, abuse, neglect, or acts of God. For the purpose of this section, “Normal Use” means in strict accordance with any documentation describing safe practices used by a professional tradesman in the industry.