BISMAT[®] 5000 (Ø 21/2 - 4")

for plastic pipes Ø $2\frac{1}{2} - 4$ " $3\frac{1}{8}$ "



Features and benefits

- two-screw clamp
- with BISMAT[®] quick locking system
- with removable spacer washers, making the clamp suitable for either location or tight fixing
- material: steel

Part No.

CR 348 9 075


CR 348 9 090

CR 348 9 110

CR 348 9 125

CR 348 9 160

- zinc plated
- noise insulating lining, EPDM rubber, green
- lining: very suitable for applications with plastic pipes
- inner part of lining is flush to improve sliding of pipe in clamp
- lining resistant to aging
- complies with Federal Specification WW-H-w171E and A-A-1192A Type 4 and Manufacturers Standardization Society MSS SP-58 and SP-69 type 12
- Plenum rated tested to ASTM E-84



The max. allowed load (Fa,z) is calculated using specific statistical methods related to the breaking load, taking into account a deflection to 1,5 mm or 2% of the maximum nominal clamp diameter.

