

Location:



# SYMMONS® Origins®

## Kitchen Faucet S-23 Series



### Specification Submittal

Model S-23



#### Feature Highlights

- Single lever kitchen faucet with red & blue indicators on handle
- Handle limit stops
- 8-3/4 inch swing spout with aerator
- Ceramic control components

- Supply has 3/8 inch copper tubing, 8-inch centers
- Metal construction, polished chrome finish
- 2.2 gpm (8.3 L/min) standard flow rate








#### Standards / Certifications

ASME A112.18.1/CSA B125.1  
NSF/ANSI 61.9, NSF/ANSI 372




#### Warranty

- Limited Lifetime - to the original end purchaser in consumer installations.
- 5 years - for commercial installations


S-23 series			
S-23-2-LP	S-23-2-W	S-23-1	S-23-3
			
<h4>Ordering Information</h4> <p><b>Model Numbers</b> <i>Append appropriate -suffix to model number.</i></p> <ul style="list-style-type: none"> <li><input type="checkbox"/> S-23 Faucet only</li> <li><input type="checkbox"/> S-23-1 Faucet with swivel spray aerator in place of hose and spray (not available in low flow).</li> <li><input type="checkbox"/> S-23-2 Faucet with hose and spray</li> <li><input type="checkbox"/> S-23-3 Faucet with hose and spray mounted on escutcheon</li> </ul>		<h4>Other Options</h4> <p><i>Append appropriate -suffix to model number.</i></p> <ul style="list-style-type: none"> <li><input type="checkbox"/> -LST 18 inch copper supply tubing</li> <li><input type="checkbox"/> -BH 20 inch (508 mm) braided hose supplies (<i>not available with -SM option for S-23-2 and S-23-3 configurations</i>)</li> <li><input type="checkbox"/> -10 10-7/8 inch swing spout with aerator</li> <li><input type="checkbox"/> -IPS 1/2 inch IPS connections</li> <li><input type="checkbox"/>  -0.5 Vandal resistant, 0.5 gpm (1.9 L/min) aerator</li> <li><input type="checkbox"/>  -1.0 1.0 gpm (3.8 L/min) aerator</li> <li><input type="checkbox"/>  -1.5 1.5 gpm (5.7 L/min) aerator</li> <li><input type="checkbox"/> -VP Vandal resistant, 2.2 gpm (8.3 L/min) aerator</li> <li><input type="checkbox"/> -VP-1.5 Vandal resistant, 1.5 gpm (5.7 L/min) aerator</li> <li><input type="checkbox"/> -NA Non-aerated, 2.2 gpm (8.3 L/min) laminar flow outlet</li> <li><input type="checkbox"/> -SM Single hole mounting (<i>not available with -BH option for S-23-2 and S-23-3 configurations</i>)</li> </ul>	
<h4>Finish Options / Modifications</h4> <p><i>Append appropriate -suffix to model number.</i></p> <ul style="list-style-type: none"> <li><input type="checkbox"/> -STN Satin nickel finish* <ul style="list-style-type: none"> <li>- Polished chrome (standard finish)</li> </ul> </li> </ul>			
<h4>Handle Options / Modifications</h4> <p><i>Append appropriate -suffix to model number.</i></p> <ul style="list-style-type: none"> <li><input type="checkbox"/> -LP Loop handle</li> <li><input type="checkbox"/> -W Lever handle 6 inch (152 mm) chrome only</li> </ul>			

### Dimensions *Origins Kitchen Faucet, S-23*




**Note:** Dimensions subject to change without notice.

### Dimensions *Origins Kitchen Faucet, S-23-W*




**Note:** Dimensions subject to change without notice.

**Dimensions** *Origins Kitchen Faucet, S-23-SM-10*




**Note:** Dimensions subject to change without notice.

**Dimensions** *Origins Kitchen Faucet, S-23-BH*



**Note:** Dimensions subject to change without notice.

## Dimensions *Origins Kitchen Faucet, S-23-SM*



**Note:** Dimensions subject to change without notice.