


## TECHNICAL SPECIFICATIONS

## **NDS D1500 Meter Boxes**

## NDS WATER METER BOXES AND COVERS

NDS 13"x 20" meter boxes and covers are injection molded of structural foam recycled polypropylene material with a melt index between 10-12. Coloring and UV stabilizers are added, along with processing lubricants when needed. The 13"x 20" body shall be tapered and have a minimum wall thickness of .25". The body shall have a double wall at the top cover seat area with a minimum thickness of .187". The cover seat area shall have 56 structural support ribs on the underside of the seat, each with a minimum thickness of 1/50". The bottom of the body shall have a 1" flange. The 13"x 20" cover shall have an average thickness of .250".





Product is not to be installed in concrete and is not to be used in vehicular applications. Weights and dimensions are nominal.

Part Number	Box Description	Cover Description	Cover Type	Color (Box/Cover)	Weight (lbs)
Drop In Box & Cover					
D1500-DISB	13"x20"x12" Jumbo Box	Drop-in Cover - Water Meter	Solid Plastic	Black/Black	13.20
D750E-DISB	13"x20"x6" Extension	Drop-in Cover - Water Meter	Solid Plastic	Black/Black	9.40
D1500-DUDISB	13"x20"x12" Dual Pipe Slot Jumbo Box	Drop-in Cover - Water Meter	Solid Plastic	Black/Black	13.49
D1500-BDDISB	13"x20"x12" Jumbo Box	Bolt Down Drop-in Cover - Water Meter	Solid Plastic	Black/Black	13.40
D1500P-DISP	13"x20"x12" Jumbo Box	Drop-in Cover - Reclaimed Water	Solid Plastic	Purple/Purple	13.40
D1500-BDDISP	13"x20"x12" Jumbo Box	Bolt Down Drop-in Cover - Reclaimed Water	Solid Plastic	Black/Purple	13.40
D1500-DIRB	13"x20"x12" Jumbo Box	Drop-in Meter Reader Cover - Water Meter	Plastic w/ Plastic Reader	Black/Black	13.20
D1500-DUDIRB	13"x20"x12" Dual Pipe Slot Jumbo Box	Drop-in Meter Reader Cover - Water Meter	Plastic w/ Plastic Reader	Black/Black	13.49
D1500-DIRG	13"x20"x12" Jumbo Box	Drop-in Meter Reader Cover - Water Meter	Plastic w/ Plastic Reader	Black/Green	13.20
D1500-DIRP	13"x20"x12" Jumbo Box	Drop-in Meter Reader Cover - Reclaimed Water	Plastic w/ Plastic Reader	Black/Purple	13.20
D1500-DICIR	13"x20"x12" Jumbo Box	Drop-in Meter Reader Cover - Water Meter	Plastic w/ Cast Iron Reader	Black/Black	14.40
D1500-DUDICIR	13"x20"x12" Dual Pipe Slot Jumbo Box	Drop-in Meter Reader Cover - Water Meter	Plastic w/ Cast Iron Reader	Black/Black	13.20
D1500-DICIRP	13"x20"x12" Jumbo Box	Drop-in Meter Reader Cover - Reclaimed Water	Plastic w/ Cast Iron Reader	Black/Purple	14.40
D1500-DICIRMPP	13"x20"x12" Jumbo Box	Drop-in Meter Reader Cover - Water Meter	Plastic w/ Cast Iron Reader	Black/Purple	13.49
D1500P-DU-DICP	13"x20"x12" Dual Pipe Slot Jumbo Box	Drop-in Meter Reader Cover - Water Meter	Plastic w/ Cast Iron Reader	Purple/Purple	14.60
Overlapping Box & Cover		*			
D1500-OLSB	13"x20"x12" Jumbo Box	Overlapping Cover - Water Meter	Solid Plastic	Black/Black	13.20
D1500-BDOLSB	13"x20"x12" Jumbo Box	Bolt Down Overlapping Cover - Water Meter	Solid Plastic	Black/Black	13.40
D1500-DUOLSB	13"x20"x12" Dual Pipe Slot Jumbo Box	Overlapping Cover - Water Meter	Solid Plastic	Black/Black	12.79
D1500-OLSP	13"x20"x12" Jumbo Box	Overlapping Cover - Reclaimed Water	Solid Plastic	Purple/Purple	13.20
D1500-OLRB	13"x20"x12" Jumbo Box	Overlapping Meter Reader Cover - Water Meter	Plastic w/ Plastic Reader	Black/Black	13.20
D1500-DUOLRB	13"x20"x12" Dual Pipe Slot Jumbo Box	Overlapping Meter Reader Cover - Water Meter	Plastic w/ Plastic Reader	Black/Black	13.20
D1500P-OLRP	13"x20"x12" Jumbo Box	Overlapping Meter Reader Cover - Reclaimed Water	Plastic w/ Plastic Reader	Purple/Purple	13.20
D1500F-OLCIR	13"x20"x12" Jumbo Box	Overlapping Meter Reader Cover - Netralimed Water  Overlapping Meter Reader Cover - Water Meter	Plastic w/ Cast Iron Reader	Black/Black	14.40
D1500-DUOLCIR	13"x20"x12" Dual Pipe Slot Jumbo Box	Overlapping Meter Reader Cover - Water Meter	Plastic w/ Cast Iron Reader	Black/Black	12.29
Drop In Cover Only	13 X20 X12 Dual Fipe Slot Julibo Box	Overlapping Meter Neader Cover - Water Meter	riastic W/ Cast Holl Headel	Diack/Diack	12.23
D1500-DISBL		13"x20" Drop-in Cover - Water Meter	Solid Plastic	Black	3.80
D1500-DISBL		•	Solid Plastic	Black	3.80
D1500-BDSB LID		13"x20" Bolt Down Drop-in Cover - Water Meter	Solid Plastic		3.80
		13"x20" Drop-in Cover - Reclaimed Water		Purple	3.80
D1500-BDDISPL		13"x20" Bolt Down Drop-in Cover - Reclaimed Water	Solid Plastic	Purple	3.80
D1500-DIRBL		13"x20" Drop-in Meter Reader Cover - Water Meter	Plastic w/ Plastic Reader	Black	
D1500-DIRGL		13"x20" Drop-in Meter Reader Cover - Water Meter	Plastic w/ Plastic Reader	Green	3.80
D1500-DIRP LID		13"x20" Drop-in Meter Reader Cover - Reclaimed Water	Plastic w/ Plastic Reader	Purple	3.80
D1500-DICIR LD		13"x20" Drop-in Meter Reader Cover - Water Meter	Plastic w/ Cast Iron Reader	Black	5.00
D1500-DICIRPLD		13"x20" Drop-in Meter Reader Cover - Reclaimed Water	Plastic w/ Cast Iron Reader	Purple	5.00
D1500-DICIMPPL		13"x20" Drop-in Meter Reader Cover - Reclaimed Water	Plastic w/ Cast Iron Reader	Purple	4.58
Overlapping Cover Only					
D1500-OLSBL		13"x20" Jumbo Overlapping Cover - Water Meter	Solid Plastic	Black	3.80
D1500-BD-OLSBL		13"x20" Jumbo Bolt Down Overlapping Cover - Water Meter	Solid Plastic	Black	3.80
D1500-OLSPL		13"x20" Jumbo Overlapping Cover - Reclaimed Water	Solid Plastic	Purple	3.80
D1500-OLRBL		13"x20" Jumbo Overlapping Meter Reader Cover - Water Meter	Plastic w/ Plastic Reader	Black	3.80
D1500-OLRP LID		13"x20" Jumbo Overlapping Meter Reader Cover - Reclaimed Water	Plastic w/ Plastic Reader	Purple	3.80
D1500-OLCIR LD		13"x20" Jumbo Overlapping Meter Reader Cover - Water Meter	Plastic w/ Cast Iron Reader	Black	5.00
Box Only					
D1500-B/O	13"x20"x12" Jumbo Box			Black	9.40
D1500-DUB/O	13"x20"x12" Dual Pipe Slot Jumbo Box			Black	8.91
D1500P B/O	13"x20"x12" Jumbo Box			Purple	9.40
D1500P-DU B/O	13"x20"x12" Dual Pipe Slot Jumbo Box			Purple	9.60
D1500-BDB/O	13"X20"X12" Jumbo Bolt Down Box			Black	9.60
D750E-EXT	13"x20"x6" Extension Only			Black	5.60

Call for additional options and availability

Properties of Unfoamed Resin							
	ASTM Test Method	Polypropylene					
Tensile Strength, Yield	ASTM D 638	3300 psi					
Density	ASTM D 792	0.915					
Durometer, Shore D	ASTM D 2240	66					
Flexural Modulus	ASTM D 790	191,000 psi					
Notched Izod Impact Strength @ 23 degrees C.	ASTM D 256	1.43 ft. lbs/in.					
Notched Izod Impact Strength @ 18 degrees C.	ASTM D 256	6.8 ft. lbs/in.					
Heat Deflection Temperature @ 66 PSI, Degrees F.	ASTM D 648	209 degrees F.					

Shipping Configuration							
	Box	Extension	Lid				
Pallet	48	36	96				
Pieces per Stack	12	7	16				
Stack per Pallet	4	4	6				
Pallet Dimensions	42"x48"x48"	42"x42"x48"	42"x42"x36"				



## **NDS Technical Services**

851 N. Harvard Ave Lindsay, CA 93247 Phone: (888) 825-4716

(559) 562-9888 Fax: (800) 726-1998

(559) 562-4488

TechService@ndspro.net www.NDSPRO.com