

VFGL-4 / VFST-27-2

VENT-FREE GAS LOG SETS

Superior Vent-Free Gas Log Sets feature realistic split oak ceramic fiber gas logs which produce glowing embers when burning, simulating the natural effects of real wood logs and coals. Made of ceramic fiber, they are light-weight and withstand extremely high temperatures.

They're designed to be used in Universal Vent-Free full-sized fireboxes, as well as masonry or factory-built wood-burning fireplaces. Choose from 18", 24" and 28" sets with a range of 14,000 to 34,000 Btu/hr for natural gas and propane gas models.

Superior Vent-Free Gas Log Sets consist of a unitized log set, burner, and lava rock. The standard and millivolt models feature a unique two-burner design to provide dual flame locations. Manually operated, the standard valve flame settings can be adjusted to high and low levels to control heat output. A millivolt valve with Hi/Lo adjustment offers an optional remote control. Superior Vent-Free See-Through Gas Log Sets consists of unitized logs, lava rock and burner, with dual burner design. A millivolt valve is standard with a separate flame height adjustment knob to control heat output.



VFGL-4



VFST-27-2

MODELS AND SPECIFICATIONS

Model	Weight	Number Of Logs	Cubic Feet	Btu/Hr Input	Min. Fireplace Opening Width	Min. Fireplace Depth
VFGL - 18 MSN-4	33 lbs.	4	3	14,000 - 25,000	20" Front / 19" Rear	14"
VFGL - 18 MSP-4	33 lbs.	4	3	14,000 - 25,000	20" Front / 19" Rear	14"
VFGL - 24 MSN-4	38 lbs.	4	3.5	17,000 - 32,000	35" Front / 27" Rear	14"
VFGL - 24 MSP-4	38 lbs.	4	3.5	17,000 - 32,000	35" Front / 27" Rear	14"
VFGL - 28 MSN-4	40 lbs.	4	4	17,000 - 32,000	38" Front / 30" Rear	14"
VFGL - 28 MSP-4	40 lbs.	4	4	17,000 - 32,000	38" Front / 30" Rear	14"
VFGL - 18 VSN-4	33 lbs.	4	3	19,500 - 25,000	20" Front / 19" Rear	14"
VFGL - 18 VSP-4	33 lbs.	4	3	19,500 - 25,000	20" Front / 19" Rear	14"
VFGL - 24 VSN-4	38 lbs.	4	3.5	25,000 - 32,000	35" Front / 27" Rear	14"
VFGL - 24 VSP-4	38 lbs.	4	3.5	25,000 - 32,000	35" Front / 27" Rear	14"
VFGL - 28 VSN-4	40 lbs.	4	4	25,000 - 32,000	38" Front / 30" Rear	14"
VFGL - 28 VSP-4	40 lbs.	4	4	25,000 - 32,000	38" Front / 30" Rear	14"
VFST-27VSN-2	35 lbs.	8	5.5	27,000 - 34,000	28" Front / 28" Rear	18"
VFST-27VSP-2	35 lbs.	8	5.5	27,000 - 34,000	28" Front / 28" Rear	18"

REMOTE CONTROL KITS

Models RCL and RCL-T Remote Control Kits can be used with millivolt log sets only. These kits consist of a receiver and a wireless hand-held transmitter. (Batteries not included).




RCL



RCL-T

ADJUSTABLE HOOD

The optional Adjustable Hood helps deflect heat away from the wall and mantel. Available in black, the Adjustable Hood easily expands from 28 inches to 48 inches, to accommodate various masonry and wood-burning fireplaces.



FAH

ADDITIONAL INFORMATION

Note: Use Superior Vent-Free Gas Log Sets in Universal Vent-Free Fireboxes. Vent-Free Gas Log Sets can be also installed in solid-fuel burning masonry and factory-built fireplaces.

Built to ANSI Z21.11.2, Z223.1 or NFPA54, Z21.60 (manual version only).

Listing Agency: Omni-Test Laboratories, Inc.

Made in the U.S.A.

Tested & Listed By  Portland Oregon USA
OMNI-Test Laboratories, Inc.

