

Specifications

PFXCH SERIES

Corrugated Water Heater Connectors



Product Features

- Stainless steel corrugated
- Kink resistant
- IAPMO listed
- NSF/ANSI 61 compliant
- AB 1953 compliant
- ASME A112.18.6
- Max. Pressure: 125 psi
- Working Temperature: 40°F – 160°F
- Max. Temperature: 180°F
- Built-in dielectric sleeve to prevent possible galvanic corrosion
- 100% leak tested



PFXCHF18N

Materials

- Tubing: Stainless steel 304 (ASTM A240)
- Nut: Chrome plated brass 3771
- Gasket: High-quality EPDM

Product Specifications

Model Number	Description	Length (in)	Length (mm)
PFXCHF18N	LF 3/4 FIPXPUSH 18 SS COR WHTR CONN	18"	457.2mm
PFXCHFT18N	LF 3/4 FIP 18 SS COR WHTR CONN	18"	457.2mm
PFXCHFT24N	LF 3/4 FIP 24 SS COR WHTR CONN	24"	609.6mm
PFXCHGT18	LF 1 FIP 18 SS COR WHTR CONN	18"	457.2mm
PFXCHGT24	LF 1 FIP 24 SS COR WHTR CONN	24"	609.6mm
PFXCHHT18	LF 1-1/4 FIP 18 SS COR WHTR CONN	18"	457.2mm
PFXCHJT18	LF 1-1/2 FIP 18 SS COR WHTR CONN	18"	457.2mm
PFXCHGFT24N	LF 1X3/4 FIP 24 SS COR WHTR CONN	24"	609.6mm
PFXCHHGT24	LF 1-1/4X1 FIP 24 SS COR WHTR CONN	24"	609.6mm
PFXCHFM18N	LF 3/4 MXF 18 SS COR WHTR CONN	18"	457.2mm
PFXCHFM24N	LF 3/4 MXF 24 SS COR WHTR CONN	24"	609.6mm
PFXCHF18NA	LF 3/4 FIPXSWT 18 SS COR WHTR CONN	18"	457.2mm
PFXCHF24NA	LF 3/4 FIPXSWT 24 SS COR WHTR CONN	24"	609.6mm
PFXCHF18P	LF 3/4 FIP X F1807 18 SS WHTR CONN	18"	457.2mm
PFXCHF24P	LF 3/4 FIP X F1807 24 SS WHTR CONN	24"	609.6mm
PFXCHF18PP	LF 3/4 FIP X F1960 18 SS WHTR CONN	18"	457.2mm
PFXCHF24PP	LF 3/4 FIP X F1960 24 SS WHTR CONN	24"	609.6mm

Warranty and Codes

These PROFLO products carry a 1-year limited warranty.



Distributed Exclusively by Ferguson and Wolseley Canada

©2021 Ferguson Enterprises, LLC 0521 2815258

FERGUSON.COM/PROFLO