



FHPH132AB1

Frigidaire 13,000 BTU
Portable Room Air
Conditioner with Heat
Pump and Dehumidifier
Mode



AVAILABLE COLORS

MORE EASY-TO-USE FEATURES

Portable Design

Easily move from room to room with caster wheels and handles, providing cool air when and where you need it.

Remote Control

Precisely control the temperature and fan speed from across the room.

Multi-Speed Fan

Enjoy more cooling flexibility with three different fan speeds.

Automatic Restart

Automatically resumes operating at its previous settings when power is restored to your unit.

SIGNATURE FEATURES

Programmable Timer

Customize times to fit your schedule for immediate comfort when you get home and preset the unit to turn on and off in half hour increments.

Dehumidifying Dry Mode

Keep your home comfortable by removing excess moisture from the air.

Supplemental Heat

Stay comfortable no matter the outside temperature. With supplemental heat, you have the option to either heat or cool your space.

Easy-to-Clean Washable Filter

Capture dust from the air and keep your air conditioner working efficiently with our easy-to-clean washable filter.

FHPH132AB1

Frigidaire 13,000 BTU Portable Room Air Conditioner with Heat Pump and Dehumidifier Mode

FRIGIDAIRE

General Specifications

Product Weight	82.65 lbs
Prop 65 Label	Yes
Refrigerant Type	R-410A
Warranty - Labor	1 Year
Warranty - Parts	1 Year
Power Type	Electric
Size	13,000 BTU
Installation Type	Free-Standing
Collection	Frigidaire

Electrical Specifications

Amps (Heat Pump)	7.5 Amps
Plug Type	LCDI 515P
Voltage Rating	115 V
Watts (Heat Pump)	850 Watts

Safety Certifications and Approvals

ETL Listed	Yes
Energy Efficiency Verification (Canada)	Yes

Dimensions and Volume

Height	27 9/10"
Width	18 7/10"
Depth	15 5/32"

Functions

24-Hour On/Off Timer	Yes
Auto Fan	Yes
Auto Restart	Yes
Continuous Drain Operation	Yes
Dry Mode	Yes
Low Voltage Start-up	Yes
Sleep Mode	Yes

Performance

Cool Area	600 sq.
DOE BTU (Cool)	8,000 BTU
ASHRAE BTU (Cool)	13,000 BTU
BTU (Heat Pump)	7,600 BTU
Combined Energy Efficiency Ratio	7.2
Dehumidification - Pints per Hour	2.8

Accessories

Included Accessory	Window Slider Kit
--------------------	-------------------

Controls

Control Type	Electronic
Remote Control	Yes

AC

Air CFM (Low)	211 CFM
Air CFM (Med)	230 CFM
Air CFM (High)	241 CFM
Air Direction Control	Swing Louver
Air Discharge	Top of Unit
Fan Speeds - Cool	3
Fan Speeds - Fan	3
Fan Speeds - Heat	3
Filter Type	Easy-to-Clean Washable Filter
Motor RPM (Low)	480 RPM
Motor RPM (Med)	550 RPM
Motor RPM (High)	620 RPM
Noise Level dBA (Low)	49 dBA
Noise Level dBA (Med)	51 dBA
Noise Level dBA (High)	52 dBA
Exhaust Hose	Single Hose
Filter Access	Yes
Filter Check Indicator	Yes
Window Mounting Kit	Yes

Note: For planning purposes only. Always consult local and national electric, gas and plumbing codes. Refer to Product Installation Guide for detailed installation instructions on the web at frigidaire.com / frigidaire.ca.

Specifications subject to change. Accessories information available on the web at frigidaire.com / frigidaire.ca

FRIGIDAIRE

USA • 10200 David Taylor Drive • Charlotte, NC 28262 • 1-800-FRIGIDAIRE • frigidaire.com
CANADA • 5855 Terry Fox Way • Mississauga, ON L5V 3E4 • 1-800-265-8352 • frigidaire.ca

FHPH132AB1
©2017 Electrolux Home Products, Inc.