


1507

LINE SET TAPE

VentureTape® 1507 is a bi-axially oriented polypropylene (BOPP) tape coated with a cold weather solvent acrylic adhesive. Designed for line set applications, VentureTape 1507 is also ideal for sealing flexible air duct and air connectors, providing easy application and superior performance and durability over a wide range of temperatures and environmental conditions.

Product Construction



Features & Benefits

- UL723 Classified (0/0 Flame/Smoke Rating)
- High performance tape performs well over a wide temperature range
- All weather acrylic adhesive applies easily at cold temperatures
- Higher adhesion and tack than traditional cloth duct tapes
- In stock product available for immediate delivery

Test	Typical Value	Typical Value (Metric)	Test Method
Product Thickness	3.0 mils	0.08 mm	PSTC-133
Peel Adhesion ^Δ	30 oz/in	8.3 N/25 mm	PSTC-101
Shear Adhesion	>24 hrs @ 2.2 psi	>24 hrs @ 15.2 kPa	PSTC-107
Tensile Strength	20 lb/in	90.4 N/25 mm	PSTC-131
Elongation	130 %	130 %	PSTC-131
WVTR	0.05 perms		ASTM E96
Service Temperature	-40 to 185 °F	-40 to 85 °C	

^Δ - 20 minute dwell
Typical values are not intended to be used for specification development. Technical data is believed to be true and accurate; Venture Tape recommends that the purchaser test for fitness of use in all applications.

Product Configurations

- Available in Black and Silver
- Standard size 2" x 60Y (50mm x 55m)

Contact Venture Tape today for a complete list of products or a free sample

Toll Free North America 800-343-1076

From United Kingdom 0-800-962-957

From Australia 1-800-122-797

www.venturetape.com

VentureTape®

GTA - NHT, Inc.
Venture Tape
30 Commerce Rd., Rockland, MA 02370
Tel 781-331-5900; Fax 781-871-0065
800-343-1076 (U.S.A.), 800-544-1024 (Canada)
Toll Free Fax 877-264-5490
www.venturetape.com

GTA

TAPES & ADHESIVES
a 3M Company