S9030

5.5A15/LED/2700K/120V
5.5 watt; A15 LED; Frosted; 2700K; Medium base; 230 Degree beam spread; 120 voltsm spread; 120 volts

Features
- Solid State LED lighting
- A shaped replacement lamp
- Long life
- Dimmable
- Approved for enclosed fixtures

Operating temperature: -25C (-13F) to a maximum of +45C (113F); Not for use in ovens



S9030

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape	Base
S9030	045923090301	120	5.5	40W	0.79	A15	Medium

ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Suggested Dimmers	Finish	MOL In Inches	MOD In Inches	Initial Lumens
E26	5.5A15/LED/2700K/120V	Dimmable	Compatible dimmers for S9030	Frosted	3-15/16"	1-7/8"	450

Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type
25000	2700	Warm White	80	230	-25C (-13F) to a maximum of +45C (+113F)	24/6	Box

ENERGY STAR	CEC Status	RoHS Compliant	Fixture Type	UL or ETL Listed	UL Classification	Warranty
ENERGY STAR	Non-Compliant Possible sub: S8572	Yes	Enclosed Rated	Yes	cULus - Damp Location Rated	5 Year Limited - 10 hour use per day

National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051