


#### "L" DIM. (121mm) 4<sup>3</sup>/<sub>4</sub>" (121mm) 1" I.P.S + WALL THICKNESS SUPPLY 11/2" (38mm) **OPENING** IN WALL CENTER LINE 16" CONNECTION THROUGH (406mm) WALL NOT SUPPLIED 141/2 BY \$LOAN (368mn CENTER LINE 4 1/8" max. (105mm) 2 1/8" min. (54mm) OF WASTE 31/4" (83mm) LONG FLUSH TUBE FIN. FIN. (for connection **FLOOR** WALI behind wall)

# Royal® Prison Model **Flushometer**



#### Description

Concealed Water Closet Flushometer, for Stainless Steel Combination Fixtures. For use with: Acorn® • Bradley® • Metcraft® (Series 3000) • Willoughby® and similar fixtures.

## Flush Cycle

☐ Model 603 Water Saver (3.5 gpf/13.2 Lpf)

☐ Model 603-1.6 Low Consumption (1.6 gpf/6.0 Lpf)

## **Specifications**

Quiet, Concealed, Diaphragm Type, Rough Brass Closet Flushometer for either left or right hand supply with the following features:

- Dual Filtered By-Pass
- Diaphragm, Handle Packing, Stop Seat and Vacuum Breaker to be molded from PERMEX™ rubber compound for Chloramine resistance
- Metal Non-Hold-Open Push Button with a Triple Seal Handle Packing
- 1" I.P.S. Wheel Handle Bak-Chek™ Angle Stop
- Adjustable Tailpiece
- High Back Pressure Vacuum Breaker
- Elbow Flush Connection and Coupling for 1½" NPT Back Inlet (for connection in the pipe chase - flush connection through the wall not provided by Sloan)
- Sweat Solder Adapter
- Exposed parts Chrome Plated

Valve Body, Cover, Tailpiece and Control Stop shall be in conformance with ASTM Alloy Classification for Semi-Red Brass. Valve shall be in compliance to the applicable sections of ASSE 1037, ANSI/ASME 112.19.6, and Military Specification V-29193.

### L Dimension

Specify the "L" Dimension for the proper length of the Push Button Assembly. The "L" Dimension is equal to the Wall Thickness (to the nearest whole inch) plus 43/4".

## **Variations**

AFD Shorter Vacuum Breaker - for use with Anti-Flood Device (Anti-Flood Device NOT provided by Sloan) \*Not required for use with Bradley Flood Buster® ☐ ES

Solenoid Operated (specify 24 VAC or 120 VAC)


ESM Solenoid Operated with Modular Plug for use with Sloan PWT Systems (24 VAC only)

 $\square$  TP Trap Primer Elbow

- For Hydraulic Operation use Flushometer Model 9603
- Prison Flushometers can also be provided in Regal® and/or Naval® Models. All rough-in dimensions remain the same.

See Accessories Section of the Sloan catalog for details on these and other Flushometer variations.





The information contained in this document is subject to change without notice.

Made in the U.S.A.

Listed by I.A.P.M.O.



SLOAN VALVE COMPANY • 10500 SEYMOUR AVE. • FRANKLIN PARK, IL 60131 PHONE: 1-800 982-5839 • FAX: 1-800 447-8329 • http://www.sloanvalve.com