

SPECIFICATION SHEET

Low Profile Medicine Cabinet




FEATURES/TYPICAL SPECIFICATIONS

- · Recess Mount Installation
 - Wall Opening/Rough-in Dimensions: 12½" x 34¼" x 3½"
- Formed and welded steel housing (WB/ST)
 - 24 gauge steel with white, heat cured, acrylic paint finish
- Frameless mirror door
 - 1/8" float glass mirror door front with polished edges (POL1)
 - 22 gauge steel door back with white, heat cured, acrylic paint finish
- 32" piano hinge with 90° stop welded to the door and mechanically fastened to the cabinet body (HG01) (1 typical)
- Magnet in white plastic cover fastened to cabinet body aligns to stainless steel striker plate on the door (1 typical)
- Reversible for left-hand or right-hand door swing
- 3/16" thick glass shelves, adjustable (ADJ) (3 typical)
- Mounting hardware, aluminum shelf brackets (3 left & 3 right typical), and a 26 gauge galvanized steel toothbrush holder with white, heat cured, enamel paint finish included
- · Standard Pallet Quantity of 32 units

Finishes:

Housing: PT01— Basic White Mirror: POL1—Polished Edge

Frame: Frameless



		Dimensions In Inches									
Model #	Description	Α	В	С	D	E	F	G	Н	J	K
663BC	MEDCAB 1DR 15X36 FMLS WB/ST	15	361/8	3/4	31/8	12	1	14	33-13/16	1	3/16

REFERENCE	QTY.	REMARKS	Project				
			Location				
			Architect				
			Engineer				
			Contractor				
			Submitted by	Date			

^{*} All models and material specifications are subject to change or withdrawal without notice.

S663BC_C12