

61" CALLAWAY

CAST IRON SLIPPER CLAWFOOT TUB - IMPERIAL FEET

SKU: 900365



FEATURES

Dimensions: 61" L x 30" W x 22- 29" H ($\pm 1/2$ ").

White feet are powder coat over cast iron. All other finishes made of plated solid brass.

Note: Due to the height of this tub, must use a Shallow Floor Flange when installing your tub drain.

Overflow option: includes Extended Pop-Up Drain with Swivel Head. Choose a Standard or Daisy Wheel overflow, which remain open to allow water into the drain, or the Press-and-Seal overflow, which can be closed for additional water depth.

Design: Traditional

Product Finish: White

Overflow Hole: Yes

Shape: Oval

Material: Cast Iron

CONTENTS





TUB PAGE 2

REVISED 07/27/2020

61" CALLAWAY

CAST IRON SLIPPER CLAWFOOT TUB - IMPERIAL FEET

SKU: 900365



FEATURES

- Length: 61"
- Width: 30"
- Height: 29-1/4"
- Tub Interior Length: 40"
- Tub Interior Width: 17"
- Water Depth To Rim: 17"
- Water Depth To Overflow: 13-1/2"
- Feet Type: Ball & Claw
- Feet Material: Cast Iron
- Tap Deck: No
- Drain Included: Optional
- Drain Placement: End
- Faucet Included: No
- Water Capacity (Gallons): 45
- Built-in Adjusters: Yes
- Tub Weight Uncrated (Lbs): 285
- Tub Weight Crated (Lbs): 395

PRODUCT IMAGE



PAGE 2

Code: 204083, 106474, 204081, 106481,
106480, 454793, 454794, 215201,
215200, 106476, 106473

All dimensions and specifications are nominal and may vary. Use actual products for accuracy in critical situations.