


## Dove Creek 3-Light Vanity Light Satin Nickel







N/A

## **SPECIFICATIONS**

MOUNTING: Wall Mount

SLOPED CEILING ADAPTABLE:

LAMPTYPE I: 3 lamps 60W Incandescent

**BULB INCLUDED:** No WATTS PER BULB: 60W TOTAL WATTAGE: 180W DIMMABLE: Yes

MATERIAL CONSTRUCTION: Steel

**ASSEMBLED DIMENSIONS:** 6.5" H × 24" L × 6" D

6.50 lbs. WEIGHT:

**BACKPLATE DIMENSIONS:** 4.92" H × 24" W

CANOPY/PLATE DIMENSIONS: N/A

**GLASS/SHADE DIMENSIONS:** 4.4" H × 5.4" L × 3.8" D

**GLASS/SHADE MATERIAL:** Glass GLASS/SHADE TYPE: Frosted **GLASS/SHADE COLOR:** White

LED BRIGHTNESS (LUMENS):

LED COLOR CORRELATED TEMPERATURE (CCT):

N/A

LED COLOR RENDERING INDEX (CRI): N/A

LED EFFICACY: N/A

LED AVERAGE RATED LIFE: N/A

**ENERGY EFFICIENT:** No

LIGHTING AMPS: N/A

**VOLTAGE:** 120V

WARRANTY: 10-Year limited warranty

**UL/ETL CERTIFICATION:** cUL/UL WET/DRY/DAMP LISTING: Damp ADA COMPLIANT: No **ENERGY STAR CERTIFIED:** No







TYPE: IOB:

ORDER CODE:

APPROVALS: