




Definite Purpose Contactors

MARS SERIES **910**

COMPONENT

MARS Definite Purpose Contactors

MARS definite purpose contactors are designed for use on refrigeration, air conditioning, and electric heating systems. They are available in one pole with shunt (one and one half pole) configurations, from 30 thru 40 amps. MARS brand definite purpose contactors are also available in 2 pole models (30 and 40 amp) and 3 pole models (30 through 75 amp). The universal mounting base allows replacement of most contactor brands. Straight-thru wiring and small size speeds installation.



Features:

- Used on air conditioning, refrigeration and electric resistance heating
- Straight-thru wiring to speed installation
- Universal mounting base
- Small, compact design

Specifications:

- ARI 780 rated
- UL and CSA recognized
- 1,000,000 cycle mechanical life

| MARS NO. | FULL LOAD AMPS | RESISTIVE AMPS | LOCKED ROTOR AMPS @ 240/277 | COIL VOLTAGE | POLES | HEIGHT | WIDTH | DEPTH |
|----------|----------------|----------------|-----------------------------|--------------|-------|--------|-------|----------|
| 91311 | | | | 24 | | | | |
| 91312 | 30 | 40 | 150 | 110/120 | 1-1/2 | 2.44 | 2.00 | 3.25 in. |
| 91313 | | | | 208/240 | | | | |
| 91411 | 40 | 50 | 240 | 24 | 1-1/2 | 2.44 | 2.00 | 3.25 in. |
| 91321 | | | | 24 | | | | |
| 91322 | 30 | 40 | 150 | 110/120 | 2 | 2.44 | 2.13 | 3.25 in. |
| 91323 | | | | 208/240 | | | | |
| 91331 | | | | 24 | | | | |
| 91332 | 30 | 40 | 180 | 110/120 | 3 | 3.00 | 2.50 | 3.25 in. |
| 91333 | | | | 208/240 | | | | |
| 91421 | | | | 24 | | | | |
| 91422 | 40 | 50 | 240 | 110/120 | 2 | 3.00 | 2.50 | 3.25 in. |
| 91423 | | | | 208/240 | | | | |
| 91431 | | | | 24 | | | | |
| 91432 | 40 | 50 | 240 | 110/120 | 3 | 3.00 | 2.50 | 3.25 in. |
| 91433 | | | | 208/240 | | | | |
| 91531 | | | | 24 | | | | |
| 91532 | 50 | 65 | 300 | 110/120 | 3 | 3.56 | 2.75 | 4.13 in. |
| 91533 | | | | 208/240 | | | | |
| 91631 | | | | 24 | | | | |
| 91632 | 60 | 75 | 360 | 110/120 | 3 | 3.56 | 2.75 | 4.13 in. |
| 91633 | | | | 208/240 | | | | |
| 91731 | | | | 24 | | | | |
| 91732 | 75 | 93 | 450 | 110/120 | 3 | 4.06 | 3.75 | 5.00 in. |
| 91733 | | | | 208/240 | | | | |

