

DESCRIPTION

Brass Construction

- Pressure balancing valve design with 1/2" PEX, CPEX, or CC Connections
- Tub outlet 8" x 7" x 1/2" copper tube

OPERATION

- Adjustable temperature limit stop to control maximum hot water temperature
- Pressure balancing mechanism maintains selected discharge temperature to \pm 3°

CARTRIDGE

- 1222 cartridge design
- Flush Plug Available with "FP" Prefix models
- Accommodates back to back installations

STANDARDS

• Third party certified to meet ASME A112.18.1/CSA B125.1, ASSE 1016, and all applicable requirements referenced therein

WARRANTY

- Lifetime limited warranty against leaks, drips and finish defects to the original homeowner
- 10 year limited warranty when used in a multifamily installation
- 5 year limited warranty when used in a commercial installation

Visit www.moen.com/support for complete details and limitations






POSI-TEMP[®] VALVE Pressure-Balancing Valve

SKU	Description
62380PF/FP62380PF	4-Port Posi-Temp PEX with CC Drop
62360PF/FP62360PF/2360PF	4-Port Posi-Temp PEX with CC Drop with Stops
62365PF/FP62365PF	4-Port Posi-Temp CPEX with CC Drop
62385PF/FP62385PF/2385PF	4-Port Posi-Temp CPEX with CC Drop with Stops
62320PF	4-Port Posi-Temp CC with CC Drop
62370PF	4-Port Posi-Temp CC with CC Drop with Stops





FOR MORE INFORMATION CALL: 1-800-BUY-MOEN www.moen.com