



DESIGN FEATURES

- · Chloramine resistant soft cones
- Exclusive POWR-TIGHT 12-point crimpmany times industry standard
- · Chloramine resistant tubing
- Withstands dramatic changes in water pressure
- Easy installation, no special tools or soldering required.

MATERIAL SPECIFICATIONS

• Working Pressure: 160 psi

Operating Temperature: 33° F - 140° F
Tubing: Reinforced PVC, NSF 61 compliant
Nuts & End Fittings: Nickel-Plated Brass

• Washers: NSF 61 Compliant

COMPLIANCES/LISTINGS

- IAPMO Certified
- NSF Compliant
- ASME A112.18.6

MIGHTYFLEX DISHWASHER CONNECTOR Specification Sheet			
KDW-148-PP		48"	
KDW-160-PP	1/2" FIP SOFT CONE X 3/8" COMP W/90° ELBOW*	60"	
KDW-172-PP		72"	
KDW-184-PP		84"	
KDW-360-PP	1/2" COMP X 3/8" COMP W/90° ELBOW*	60"	
KDW-448-PP	1/2" FIP SOFT CONE X 1/2" FIP SOFT CONE	48"	
KDW-460-PP		60"	
KDW-472-PP		72"	
KDW-484-PP		84"	
KDW-636-PP	3/8" COMP X 3/8" COMP W/90° ELBOW*	36"	
KDW-648-PP		48"	
KDW-660-PP		60"	
KDW-672-PP		72"	
KDW-684-PP		84"	
KDW-784-PP	1/2" SOFT CONE COMP X 1/2" SOFT CONE COMP W/90° ELBOW*	84"	
KDW-810-PP**	3/8" VANGUARD PEX	10"	
KDW-848-PP**	X	48"	
KD\\\/-872-PP**	3/8" COMP W/90 ELBOW*	72"	

*Note: Elbow is 3/4" NPT Male x 3/8" Compression Male



3689 Arrowhead Drive, Carson City, NV 89706
Phone (800) 854-3215 Fax (800) 243-1777
E-mail sales@Ispproducts.com Website www.lspproducts.com

Content matter is subject to change at any time. It is the user's responsibility to ensure the most updated revisions are obtained. AF/S-2006 (04-08) Rev 3

Product Submittal			
Job Name			
Date			
Part Number	Quantity		
Architect			
Contractor	•		

^{**}Note: use when angle stop valve is not needed (manifold system)