



# LANCASTER

## WATER TREATMENT

## ATLAS FILTER HOUSINGS

40 YEARS OF QUALITY DESIGN AND DEVELOPMENT HAVE RESULTED IN NEW MATERIALS, NEW MOLDING METHODS, AND EXPERTISE TO CREATE THE HIGHEST QUALITY POINT OF ENTRY CARTRIDGE FILTRATION DESIGNS AVAILABLE.

### FEATURES

- Three piece design available on 2" housings for ease of install
- Heavy duty stainless steel or double ring inlet and outlet design for installation integrity
- 120 psi pressure rating on both clear and blue housings
- Big 4" housings with optional 3/8" bottom drain for ease of service
- Patented twist off pressure release valve
- Patented elastomer construction
- Kits include housing, wrench and bracket

Model No.	Description	Flow Rate	Width x Height	In/Out	
				Size	Thread Type
<b>Blue Housing Kits</b>					
210-H-75SS-B-KIT	10" Three Piece Filter Housing	8 GPM	2 x 10	3/4"	Stainless Steel NPT
220-H-75SS-B-KIT	20" Three Piece Filter Housing	15 GPM	2 x 20	3/4"	Stainless Steel NPT
410-H-I-B-KIT	4 x 10" Big Filter Housing	18 GPM	4 x 10	1"	Double Ring Plastic NPT
<b>Clear Housing Kits</b>					
210-H-75SS-C-KIT	10" Three Piece Filter Housing	8 GPM	2 x 10	3/4"	Stainless Steel NPT
220-H-75SS-C-KIT	20" Three Piece Filter Housing	15 GPM	2 x 20	3/4"	Stainless Steel NPT
410-H-I-C-KIT	4 x 10" Big Filter Housing	18 GPM	4 x 10	1"	Double Ring Plastic NPT

### ACCESSORIES

Model No.	Description
<b>Drain Kit</b>	
410-DRKT	Bottom Drain Kit
<b>Pressure Gauge</b>	
410-GAUGE	1/8" BSP Pressure Gauge - (two needed for accurate readings)



10" Three Piece Filter Housing



20" Three Piece Filter Housing



10" Big Filter Housing

# ATLAS CARTRIDGE FILTERS

LANCASTER AND ATLAS OFFER THE MAXIMUM FOR: PRODUCTIVITY, RELIABILITY, AND FLEXIBILITY

## FEATURES


- Wound polypropylene thread and melt-blown polypropylene from 1 to 50 micron available \*
- 2.5" diameter - lengths available 10" and 20"
- 4.5" diameter - lengths available 10" and 20"
- Microban impregnated cartridges available
- KX carbon block available in taste and odor, VOC, cyst-lead, and chloramine

\*Lower micron ratings available upon request

Model No.	Description	Micron	Width X Height	Seal Type
<b>Sediment Cartridges</b>				
210-C5-WT	Wound Polypropylene Thread	5	2 x 10	Standard double open end antimicrobial flat
210-C10-WT		10	2 x 10	
210-C25-WT		25	2 x 10	
220-C5-WT		5	2 x 20	
220-C10-WT		10	2 x 20	
220-C25-WT		25	2 x 20	
410-C5-WT		5	4 x 10	
410-C10-WT		10	4 x 10	
410-C25-WT		25	4 x 10	
210-C5-MB	Melt-Blown Polypropylene Smooth	5	2 x 10	
210-C10-MB		10	2 x 10	
210-C25-MB		25	2 x 10	
220-C5-MB		5	2 x 20	
220-C10-MB		10	2 x 20	
220-C25-MB		25	2 x 20	
410-C5-MB		5	4 x 10	
410-C25-MB		25	4 x 10	
<b>Carbon Cartridge</b>				
210-C5-CA	Activated Carbon Block (Coconut Shell)	5	2 x 10	Standard double open end antimicrobial flat



Wound Polypropylene Thread



Melt-Blown Polypropylene Smooth



Activated Carbon Block (Coconut Shell)