

RIDGID

FlexShaft™ Machines Clears From 1¼" to 4" Drain Line



NEW RIDGID FlexShaft machines are lightweight, compact and highly efficient machines that deliver wall-to-wall clean in 1¼" to 4" drain lines up to 70'. FlexShaft machines can also be operated while an inspection camera is in the line, letting you see while you clean. No other soft blockage expert can do that.

- **Wall-To-Wall Clean:** Chain knockers expand for full pipe cleaning
- **Simultaneous Camera Use:** FlexShaft machines let you keep your camera in-pipe while you work
- **Increase Productivity:** Faster setup and cleanup, quick cleaning, and cordless convenience for additional time savings
- **Customize Your Machine:** A full range of chain knockers and accessories are available

RIDGID® FlexShaft machines utilize specialized chain knockers attached to a flexible cable that are spun at high speeds by a cordless drill attached to the center drive shaft. Since the cable spins inside a durable nylon sheath that is housed within a fully contained drum, there is less jobsite mess.



SPECIFICATIONS

Model	K9-102	K9-204
Drain Capacity (Nom.)	1 1/4" to 2" (32 – 50 mm)	2" to 4" (50 – 100 mm)
Cable Diameter (without Sheath)	1/4" (6 mm)	5/16" (8mm)
Cable Assy. Diameter (with Sheath)	3/8" (9,5 mm)	1/2" (12,7 mm)
Cable Assembly Length	50' (15,2 m)	70' (21,3 m)
Rotational Speed	Maximum 2500 RPM	Maximum 2500 RPM
Drill Attachment	5/16" Hex (8 mm)	5/16" Hex (8 mm)
Weight (without Drill/Knocker)	24.3 lbs. (11,0 kg)	37.3 lbs. (16,9 kg)
Dimension (without Drill)	19.2" x 7.5" x 22.1" (488 mm x 191 mm x 562 mm)	21.1" x 10.8" x 24.2" (536 mm x 274 mm x 615 mm)
Operating temperature	20°F to 140°F (-6°C to 60°C)	20°F to 140°F (-6°C to 60°C)

ORDER INFORMATION

CATALOG NO.	MODEL NO.	DESCRIPTION	WEIGHT	
			(lb.)	(kg)
64263	K9-102 NA	FlexShaft, 1 1/4" - 2" Pipes Includes: 50' 1/4" cable and kit*	29.5	13,4
64273	K9-204 NA	FlexShaft, 2" - 4" Pipes Includes: 70' 5/16" cable and kit**	43.5	19,7

* K9-102 includes: K9-102 1 1/4" & K9-102 2" Knockers, FlexShaft 4 oz Lubricant, PVC 1 1/4" & PVC 1 1/2" Attachments, Hex Key 4 mm T-handle Tool, Hex Key 3 mm T-handle Tool, RIDGID Tool Bag, K9-102 & K9-204 Manual Pack, Sheath Stock.

** K9-204 includes: K9-204 2" & K9-204 4" Knockers, FlexShaft 4 oz Lubricant, Hex Key 4 mm T-handle Tool, Hex Key 3 mm T-handle Tool, RIDGID Tool Bag, K9-102 & K9-204 Manual Pack, Sheath Stock.



Chain Knockers

- All pipe types
- For soft blockages and grease

ACCESSORIES

CATALOG NO.	DESCRIPTION
64283	FlexShaft Knocker, 1/4" cable, 1 1/4"-2" pipe, single chain, carbide tip
64288	FlexShaft Knocker, 1/4" cable, 2" pipe, 2 chain, carbide tip
64293	FlexShaft Knocker, 1/4" cable, 1 1/4"-2" pipe, single chain
64298	FlexShaft Knocker, 1/4" cable, 2" pipe, 2 chain
64308	FlexShaft Knocker, 5/16" cable, 2" pipe, 2 chain, carbide tip
64313	FlexShaft Knocker, 5/16" cable, 3" pipe, 3 chain, carbide tip
64318	FlexShaft Knocker, 5/16" cable, 4" pipe, 3 chain, carbide tip
64323	FlexShaft Knocker, 5/16" cable, 2" pipe, 2 chain
64328	FlexShaft Knocker, 5/16" cable, 3" pipe, 3 chain
64333	FlexShaft Knocker, 5/16" cable, 4" pipe, 3 chain
64338	RIDGID FlexShaft Lubricant, 8 oz
64343	FlexShaft 1/4" Assembly, 50' cable, sheath, couplings
64348	FlexShaft 5/16" Assembly, 70' cable, sheath, couplings
64363	RIDGID Modified Wallpipe 1 1/4"
64368	RIDGID Modified Wallpipe 1 1/2"
64643	FlexShaft 1/4" Sheath Stock, 12"
64648	FlexShaft 5/16" Sheath Stock, 12"



Carbide Tipped Chain Knockers

- Hard walled pipes
- For soft blockages, grease, scale and roots

RIDGID.COM/FLEXSHAFT



All sales subject to Ridge Tool Company Terms and Conditions of Sales. Catalog Sheet No. R-19-C (319) Effective Date: May 1, 2019
 ©2019 RIDGID, Inc. The Emerson logo and RIDGID logo are registered trademarks of Emerson Electric Co. or RIDGID, Inc. in the U.S. and other countries.
 All other trademarks belong to their respective holders.