

1111


3000K

80



Fleming LED Bath Bar Light 24" Satin Nickel





SPECIFICATIONS

MOUNTING: Wall Mount

SLOPED CEILING ADAPTABLE:

I lamp 23W LED LAMPTYPE I:

BULB INCLUDED: No

WATTS PER BULB: 23W

TOTAL WATTAGE: 23W

DIMMABLE: No

MATERIAL CONSTRUCTION: Steel

ASSEMBLED DIMENSIONS: 4.38" H × 5" L × 24" D

WEIGHT: 3.00 lbs.

BACKPLATE DIMENSIONS: 5" H × 5" W

CANOPY/PLATE DIMENSIONS: N/A **GLASS/SHADE DIMENSIONS:** N/A **GLASS/SHADE MATERIAL:** Acrylic GLASS/SHADE TYPE: Frosted **GLASS/SHADE COLOR:** N/A

LED BRIGHTNESS (LUMENS):

LED COLOR CORRELATED TEMPERATURE (CCT):

LED COLOR RENDERING INDEX (CRI):

LED EFFICACY:

49.84

LED AVERAGE RATED LIFE: 35000 hours

ENERGY EFFICIENT: Yes

LIGHTING AMPS: 0.5

VOLTAGE: 120V

WARRANTY: 10-Year limited warranty

UL/ETL CERTIFICATION: ETL WET/DRY/DAMP LISTING: Damp ADA COMPLIANT: No **ENERGY STAR CERTIFIED:** No







TYPE: IOB:

ORDER CODE:

APPROVALS: