

S2257 PAR38 Halogen

70PAR38/HAL/XEN/FL/120V

Lamp Type	Halogen
Bulb Type	PAR38
Base Type	E26SK
Wattage	70
Color Temperature	3000
Color Rendering Index CRI	99



Lighting Facts Per Bulb

Brightness 1380 lumens

Estimated Energy Cost \$8.43

per year, based on 3 hrs/day, 11c/kWh.
Energy cost depends on utility rates and light use.

Average Life 1.4 years

Based on 3 hrs/day

Light Appearance



Energy Used 70 watts

Product Information

Features

- Energy Saving Halogen
- Bright, Crisp light
- Indoor / Outdoor
- Uniform light output

Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S2257	Halogen	*	120	70	90	PAR38	Medium Skirted
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
E26SK	70PAR38/HAL/XEN/FL/120V	ND	n/a	5 5/16	4 3/4	1380	1500
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
3000	Warm White	99	30	15	Box	n/a	Yes