

\$9580 T10 LED 4.5T10/LED/E26/27K/120V

Lamp Type	LED			
Bulb Type	T10			
Base Type	E26			
Wattage	4.5			
Color Temperature	2700			
Color Rendering Index CRI	80			
Warranty	3 Year Limited			



Lighting Facts Per Bulb

Brightness	430 lumens
Estimated Energy Cost	\$0.48
per year, based on 3 hrs/ Energy cost depends on use.	•
Average Life	13.7 years
Based on 3 hrs/day	
Light Appearance	е
Warm	Cool
2700 K	
Energy Used	4 watts

Product Information

Features

- LED with a traditional incandescent look and feel
- Omni-directional light source
- Smooth dimming
- Replaces up to 40 watt lamps
- Long life 15,000 hours
- Damp Location
- UL listed for totally enclosed fixtures

Dimmer Compatibility

- Leviton DSE06
- Cooper TAL06P-C1
- Lutron Nova TCL

Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S9580	LED	*20045923095805	120	4.5	40	T10	Medium
ANSI Base	Lamp Code	Dimmable/Non- Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
E26	4.5T10/LED/E26/	27K/120 V/ es	n/a	5	1 1/4	430	15000
			Beam Spread				
Kelvin Temp	Color	CRI	Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
2700	Warm White	80	360	24	Box	n/a	Yes

Satco Products Inc. 110 Heartland Blvd., Brentwood, NY 11717 1-800-437-2826 • Fax 631-243-2027 www.satco.com

Copyright © 2016 Satco Products, Inc. All Rights Reserved. Specifications subject to change