CRAFTMADE



Laval 44 - LAV44-LK

Laval 44 Ceiling Fan (Blades Included)

Color





The versatile Laval ceiling fan is designed to fit any space. With the selection of finishes available, Laval is an easy decision.

- Standard, 3-Speed Reversible Motor
- 6" Downrod (Included)
- 44" Blades (Included)
- Integrated LED Light Source (Dimmable)
- Dual Mount (Flat or Angled Ceiling)

Specs

Blade Sweep Opt (in.)	44
Blades	4
Blade Pitch (deg)	14
Motor Size (MM)	153x15
Amps at High Speed	0.47
Watts (Hi Speed)	56.60
Energy Guide Watts	35
Energy Guide CFM	2947
Energy Guide CFM_Watts	84
Energy Guide Est. Yearly	10
Energy Cost	
	4 5 4 6 0

4,546.000 High Speed (CFM) Low Speed (CFM) 1,783.000 Shipping Weight (lbs.) 18.50 Carton Size (CU FT) 2.09 **Blade Options** Fits Only 3000 **Bulb CCT Bulb Wattage**

UCI-2000-2 Remote & Wall Controls **Compatible Control**

Types CRI

Integrated Light Kit **Light Kit Options**

1200 Lumens

Dimensions

15 24
15.34
11.82
10.75
5.85
9.02
5.40
8.85
9.02
6

