

# Iron/Tones® Top-/Under-Mount Kitchen Sink K-5707

### Features

- 33-inch minimum base cabinet width for top-mount installation.
- 36-inch minimum base cabinet width for undermount installation.
- Single bowl.
- 9" depth provides generous workspace.
- No faucet holes.

### Material

• KOHLER<sup>®</sup> enameled cast iron.

### Installation

• Top-mount or undermount.

### **Recommended Products/Accessories**

K-8801 Sink Strainer K-8799 Sink Strainer K-23726 Drain treatment K-23725 Cast iron cleaner

### **Optional Products/Accessories**

K-8342 Sink Rack K-11352 Disposal Flange with Stopper K-9000 P-Trap 1411886 Undermount kit 23 in.



# Codes/Standards

ASME A112.19.1/CSA B45.2

## KOHLER<sup>®</sup> Enameled Cast Iron Kitchen Sink Lifetime Limited Warranty

See website for detailed warranty information.

### **Available Colors/Finishes**

Color tiles intended for reference only.


Color	Code	Description
	0	White
	FF	Sea Salt™
	96	Biscuit
	47	Almond
	FD	Cane Sugar™
	NY	Dune
	95	lce™ Grey
	G9	Sandbar
	33	Mexican Sand™
	K4	Cashmere
	FT	Basalt
	58	Thunder™ Grey
	20	Suede
	KA	Black 'n Tan
	FP	Caviar
	7	Black Black™
	GRL	Grey Lavender
	DGB	Indigo Blue





# Iron/Tones®

Top-/Under-Mount Kitchen Sink K-5707



## **Technical Information**

All product dimensions are nominal.		
Installation:	Undermount, Top-mount	
Min. base cabinet width:	36" (914 mm)	
Bowl area (Only):	Length: 30-5/16" (770 mm) Width: 16-1/16" (408 mm) Bowl depth: 9" (229 mm) Water depth: 9" (229 mm)	
Drain hole:	3-7/8" (98 mm)	
Template:	1043168-7, required, included	

## Notes

Install this product according to the installation instructions.

Countertop manufacturer or cutter must use the cut-out template provided with the product, or a current one provided by Kohler Co. (call 1-800-43-FOCUS). Kohler Co. is not responsible for cut-out errors when the incorrect cut-out template is used.

