SPECIFICATIONS

Certifications / Qualifications	
Commercial Grade	Yes
Certifications/Qualifications	
ADA Compliant	Yes
Energy Star	Yes
Title 24 Compliant	Yes

Dimensions

Base Backplate 7.50 DIA Weight 0.50 LBS Height from center of Wall opening 3.75" (Spec Sheet)

Height 1.25" Width 7.50"

Electrical

Input Voltage Single(120)V

Supply Wire (Degrees) 90

Light Source

Delivered Lumens 1000 Dimmable Yes

Dimmable Notes This LED is compatible with most standard incandescent dimmers, LED dimmers, and

electronic low voltage dimmers. For more information, go to Kichler.com\dimming.

www.kichler.com/warranty

Equivalent Light Source Incandescent Expected Life Span (Hours) 40000 Lamp Included Integrated Light Source LED 18.5W Max or Nominal Watt # of Bulbs/LED Modules 1

Mounting/Installation

Mountable on Wall or Ceiling Yes Interior/Exterior Interior Location Rating Wet Flush Mount Mounting Style Mounting Weight 0.50 LBS

Photometrics

Color Rendering Index 90 Kelvin Temperature 3000K

FIXTURE ATTRIBUTES

Housing

Diffuser Description White Polycarbonate

Primary Material STEEL

Product/Ordering Information

SKU 43848WHLED30T

Finish White Style Other

UPC 783927531702

Finish Options

Brushed Nickel

Olde Bronze

White



ALSO IN THIS FAMILY





43848OZLED30T

43848WHLED27T