


9601-P, 9601-P-TRM, 9601PTRMTC Shower Trim



Specification Submittal		
Feature Highlights	Options/Modifications	
 Origins Shower System or Trim Requires Temptrol® Pressure Balancing Shower Valve (included with 9601-P) Adjustable stop screw to limit handle turn (included with 9601-P) Tri-star handle 1 mode showerhead with easy to clean nozzles 2.5 gpm (9.5 L/min) flow restrictor Tub spout not included Components shall be metal and nonmetallic construction, plated in standard Polished Chrome finish Available with TA-10 flow control spindle and T-12A cap assembly for Temptrol valve bodies installed with Test Cap (order p/n 9601PTRMTC) 	□ -1.2	
	□ -B Brass escutcheon (chrome only)	
Model Numbers □ 9601-P Shower Trim with Temptrol Pressure Balancing Shower Valve □ 9601-P-TRM Shower Trim, Temptrol Pressure Balancing Shower Valve ordered separately □ 9601PTRMTC Shower Trim with TA-10 flow control spindle and T-12A cap assembly, must order Temptrol valve with Test Cap	□ -CHKS Integral check stops - for use in installations where a positive shut-off device is used downstream of mixing valve □ -D □ Brass dome cover (chrome only) □ -L1 □ -LAM Metal finish insert handle □ -LP Loop handle	
Compliance	□ -REB Rebuild trim kit, includes TA-10 and TA-4	
 ASME A112.18.1/CSA B125.1 WaterSense @ 2.0 gpm/1.75 gpm/1.5 gpm Buy American Act (9601-P only) 	□ -VP Vandal resistant escutcheon screws in place of standard screws □ -X Integral service stops - allows water shut off a valve for service	
Warranty	Note: Append appropriate -suffix to model number.	
Limited Lifetime - to the original end purchaser in consumer/residential installations. 5 Years - for industrial/commercial installations. Refer to www.symmons.com/warranty for complete warranty information. Go to www.symmons.com/register to register your Symmons product.		

Dimensions



Measurements	
Α	6-3/8", 162 mm
В	3-1/2", 89 mm
С	2-7/8", 73 mm
	Shower Valve Hole Size
D	Min. Ø 3", 76 mm
	Max. Ø 4", 102 mm
Е	Ref. 77", 1956 mm
F	Rough-in
	2-3/8" ± 1/2", 60 mm ± 13 mm
G	Ref. 42", 1067 mm
Н	Ø 2-1/2", 64 mm
Ι	Ø 2-3/4", 70 mm
J	2-1/8", 54 mm
K	Ø 5-3/4", 146 mm

Notes:

- 1) Valve body and piping not included and shown as reference only.
- 2) Plaster shield (p/n T-176) for dry wall, plaster or other type walls 1/2" or greater.
- 3) All dimensions measured from nominal rough-in (see F as reference).
- 4) Dimensions subject to change without notice.