



STANDARD DENSITY PTFE PIPE THREAD TAPE

Product Features

Chemical Properties:	>99.5% Polytetrafluoroethylene
Tape Color:	Bright White
Thickness (+.0005/- .0005):	0.0035"
Available widths:	1/2" (12.7mm) 3/4" (19.1mm) 1" (25.4mm)
Available lengths:	260" (660cm) 520" (1321cm)
Elongation (+/- 2%):	Minimum of 50%
Density (+/- 5%):	0.4 g/cm ³
Pressure Rating:	up to 10,000psi
Temperature:	-450°F to 500°F (-268°C to 260°C)
Standards/Approvals:	MIL Spec T-27730A
Incompatibilities:	Avoid using with Molten Alkali, Halogen and Fluorine products at high temperature and pressure. Not for use on liquid fuels such as gasoline or diesel.
Usage:	To be used on all types of threaded fittings for passage of potable and non potable water, most chemicals, oxygen, liquid and natural gas, hydraulic lines, and high-pressure lines up to 1-1/2" in diameter.
Shelf Life:	Unlimited
Country of Origin:	China



Usage

To be used on all types of threaded fittings for passage of potable and non potable water, most chemicals, oxygen, liquid and natural gas, hydraulic lines, and high-pressure lines not exceeding 1-1/2" in diameter

Product Specifications

White Standard Density PTFE Thread Tape	Width	Length
PSTTD260	1/2" (12.7mm)	260" (660cm)
PSTTD520	1/2" (12.7mm)	520" (1321cm)
PSTTF260	3/4" (19.1mm)	260" (660cm)
PSTTF520	3/4" (19.1mm)	520" (1321cm)
PSTTG520	1" (25.4mm)	520" (1321cm)

Warranty and Codes

This PROSELECT product carries a 1-year limited warranty.