

Technical Product Specifications

Supurr-Flex® pure aluminum, multi-layered flexible metallic duct - UL Listed, Clothes Dryer **Transition Duct**



Supurr-Flex® Clothes Dryer Transition Duct

Pressure Loss Diagram

10,000 5.000 4,00 3,000 2,000 NCHES TO DUCT DIAMETER 1,000 700 400 300 200 100 70 50 PRESSURE DROP

1 -	(IN. W.G. PER 100 FT.)
5/06	
© 2006	NON DO D
	ION • P.O. Box 50057 • Indianapolis, IN 46250 • www.deflecto.com
DEFLECTO/Canada Ltd	1. • St. Catharines, Ontario • Canada L2M 3Y2
Deflecte's policy is a	no of continual product improvement in decide and manufacturing

Model No.	Description		
F0405B	Supurr-Flex® multi-layered flexible duct		
Fo4o8B	Supurr-Flex® multi-layered flexible duct		
FCo4o5B	Supurr-Flex® multi-layered flexible duct		
FCo4o8B	Supurr-Flex® multi-layered flexible duct		

Performance Data

for uninsulated aluminum, multi-layered flexible metallic duct

Maximum Velocity

• 5000 FPM / 25m/sec

Maximum Rated Pressures


- all diameters 10" W.C/ 2.5Kpa Pos.
 3"-6"dia., .5" W.C/.12 Kpa Neg.

Operating Temperature Range

- 0 F to 265 F/-18C to 130C Intermittent
 - UL Listed Clothes Dryer Transition Duct Listing No.: 2158A

General Information

- available in 4" (101mm) dia and lengths of 5' (1.5m) and 8' (2.4m)
- UL Listed on this product is for installations of 8 ft. (2.4m) or less
- best for clothes dryer duct, fresh air intake and non-insulated ventilation duct



Model No.	Α	length	notes
F0405B	4"dia.	5 ft.	
Fo4o8B	4"dia.	8 ft.	
FCo4o5B	4"dia.	5 ft. 1.5m	with plastic clamps
FCo4o8B	4"dia.	8 ft. 2.4m	with plastic clamps