


# 12,000 BTU/H WALL MOUNTED IDU

SUBMITTAL COVER SHEET

PROJECT NAME	
REFERENCE	
SUBMITTED BY	



CAPACITIES		
Cooling Capacity (BTU/hr)	Rated	12000
Heating Capacity (BTU/hr)	Rated	12000
ELECTRICAL DATA		

ELECTRICAL DATA		
Voltage/Phase/Frequency	208–230V, 1 Phase, 60 Hz	

LINE SET REQUIREMENTS			
Connection Type	Flare		
Liquid	Ø1/4" (Ø6.35mm)		
Gas	Ø1/2" (Ø12.7mm)		
Drain Port O.D. / Drain Hose I.D.	Ø5/8" (Ø16mm)		

INDOOR UNIT FAN DATA			
Air Flow (CFM)	Low	147	
	Medium	212	
	High	306	
Туре	DC		
RLA	0.25		
Sound Pressure (dB(A))	Low	25	
	Medium	30	
	High	36.5	

INDOOR UNIT DIMENSIONS				
Unit Dimensions	Width	31 9/16"		
	Depth	7 7/16"		
	Height	11 11/16"		
Carton Dimensions	Width	34 7/16"		
	Depth	11 1/4"		
	Height	14 15/16"		
Net Weight	18.7 lbs.			
Gross Weight	24.3 lbs.	-		

### **PRODUCT FEATURES**

- Wireless Remote Control with "Follow Me" Technology
- Auto Restart
- Auto Changeover
- 24-hour Timer
- Self Clean Function












**DIMENSIONS - DRAW12F1A** 

#### **Unit Dimensions**





# **Mounting Plate Dimensions**



## **Clearance Distances**

