

Project Name

Location

Prepared By



## NUVO 62-1165

10" LED DISK LIGHT WHITE

Notes

[www] 03-22-2021 04:50:53

### General

Status	Active
Finish	White
Wattage	12
Style	Contemporary
CCT (Kelvin)	3000
Color Temperature	Warm White
Width (in.)	9.81
Height (in.)	1.44
Indoor or Outdoor Fixture	Indoor

### Specifications

Technology	LED
CRI	90
Lumen Output	700
Rated Hours	50000
Voltage	120V
Dimmable	Yes - Dimmable
Weight (lb.)	0.74
Fixture Shape	Round
Fixture Type	Disk Light
Operating Temperature	-17C (+1.4F) to a maximum of +46C (+114.8F)

### Compliance

Safety Listing	cETLus
Location Rating	Damp
UL Application	Ceiling
Energy Star	Yes
ES Unique ID	ESID-2303533
California Status	Not T24 Compliant
California Prop 65	Lead
RoHS Compliant	Yes

### Additional Information

Additional Information	Durable White Polymer Lens
Warranty	5 Year Limited - Fixtures