

Project Name

Location

Prepared By



NUVO 62-1265

10" LED DISC LIGHT - HIGH LUMEN

Notes

[www] 03-22-2021 04:50:53

General

Status	Active
Finish	White
Wattage	21.5
Style	Contemporary
CCT (Kelvin)	3000
Color Temperature	Warm White
Width (in.)	9.81
Height (in.)	1.44
Indoor or Outdoor Fixture	Indoor

Specifications

Technology	LED
CRI	90
Lumen Output	1200
Rated Hours	50000
Voltage	120V
Dimmable	Yes - Dimmable
Weight (lb.)	0.85
Fixture Shape	Round
Fixture Type	Disk Light
Operating Temperature	-17C (+1.4F) to a maximum of +46C (+114.8F)

Compliance

Safety Listing	cETLus
Location Rating	Damp
UL Application	Ceiling
Energy Star	Yes
ES Unique ID	ESID-2326387
California Status	Not T24 Compliant
California Prop 65	Lead
RoHS Compliant	Yes

Additional Information

Warranty	5 Year Limited - Fixtures
----------	---------------------------