

Project Name

Location

Prepared By



SATCO S29312

9.8WLED/RDL/5-6/27K/120V

Notes

[www] 03-22-2021 04:50:59

General

Status	Active
Recessed Can Size	5-6 in.
Wattage	9.8
Voltage	120V
Finish	White
CCT (Kelvin)	2700
Color Temperature	Warm White
Lumen Output	650
Indoor or Outdoor Fixture	Indoor

Specifications

Technology	LED
CRI	90
Beam Angle	90
Rated Hours	35000
Operating Temperature	-20C (-4F) to a maximum of +40C (+104F)
Dimmable	Yes - Dimmable

Dimensions

Width (in.)	7.38
Height (in.)	2.31
Weight (lb.)	0.88

Compliance

Safety Listing	cULus Classified
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2308994
California Status	Non-Compliant
California Prop 65	Lead
RoHS Compliant	Yes

Additional Information

Additional Information	Trim material is Thermo Plastic; Trim color is White
Warranty	5 Year Limited - Fixtures